

xulm06031h60

photo-electric sensor - XUL - reflex - kit - Sn 6m -
24..240VAC/DC - cable 2m



Main

Range of product	OsiSense XU
Series name	Application tertiary sector
Electronic sensor type	Photo-electric sensor
Product specific application	Access detection
Sensor name	XUL
Sensor design	Compact
Material	Plastic
Detection system	Reflex
Emission	Infrared
[Sn] nominal sensing distance	6 m with reflector 50 x 50 mm
Wiring technique	5-wire
Cable length	2 m
Sale per indivisible quantity	1

Complementary

Enclosure material	ABS
Lens material	PMMA
Type of output signal	Discrete
Output type	Relay
Discrete output function	1 C/O
Output function governance	Light
Electrical connection	Cable
Cable composition	5 x 0.34 mm ²
Wire insulation material	PVC
Cable outer diameter	6 mm
Status LED	1 LED (yellow) for output state
Supply circuit type	AC/DC
[Us] rated supply voltage	20...240 V AC/DC
Supply voltage limits	20...264 V AC/DC
Output voltage	<= 250 V AC
Switching capacity in mA	0.5 A (cos φ = 0.4 for 0.5 million cycles at 1 operating cycle per second at 250 V) 2 A (cos φ = 1 for 0.5 million cycles at 1 operating cycle per second at 250 V)
Switching frequency	<= 20 Hz
Power consumption in W	<= 2 W
Delay first up	<= 60 ms
Delay response	<= 25 ms
Delay recovery	<= 25 ms
Electrical durability	500000 cycles, switching capacity: 2000 mA, cos f = 1, 60 cyc/mn at 250 V 500000 cycles, switching capacity: 500 mA, cos f = 0.4, 60 cyc/mn at 250 V
Depth	45 mm
Height	70 mm
Width	18 mm
Product weight	0.3 kg

Environment

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Product certifications	CE
Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...70 °C
Vibration resistance	7 gn, amplitude = +/- 2 mm (f = 10...55 Hz) conforming to IEC 60068-2-6
Shock resistance	20 gn (duration = 11 ms) conforming to IEC 60068-2-27
IP degree of protection	IP67 (indoor use) conforming to IEC 60529

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS	Compliant - since 0935 - Schneider Electric declaration of conformity
Product environmental profile	Available
Product end of life instructions	Available