



Cordless Circular Saw Blades

Features

- Heavy duty tungsten carbide tips maintain cutting edge for longer blade life.
- Thin kerf blade design - yields more cuts per charge by minimising battery drain.
- Triple action sharpening process which grinds the tip to a razor sharp edge for a smooth finish.
- Specifically designed for use with DeWALT Cordless Trimsaws. The range comprises of blades for cutting wood and for cutting plastic & non-ferrous metals.



Cordless Circular Saw Blades

Cat No.	Blade Diameter mm	Bore Size mm	Tooth Count	Kerf mm	Hook Angle	Grind	Applications	Pack Qty	M.O.Q.	Barcode	List Price ex. VAT
DT1200XM	136	10	16	1.5	+20	ATB	For fast cutting in wood	1	1	5011402378159	29,80
DT1201XM	136	10	24	1.5	+20	ATB	For fine finish in wood	1	1	5011402370160	31,85
DT1202XM	136	10	30	1.5	+3	Flat top	For cutting non-ferrous metals less than 3 mm thick and for an extra fine finish in wood	1	1	5011402378173	34,00
DT1203QZ	165	10	16	1.5	+20	ATB	For fast rough cutting in wood	1	1	5035048031056	30,60
DT1204QZ	165	10	24	1.5	+20	ATB	For fine cross cutting in wood	1	1	5035048031063	33,15
DT1205QZ	165	10	36	1.5	+3	Flat top	For fine crosscutting in wood, and cutting Non Ferrous Metal	1	1	5035048031186	35,70
DT1210XJ	173	20	40	2.2	0	MTCG	For clean cutting in ferrous metals	1	1	5035048056431	85,00