

D25135K-QS

SDS-plus 800W 2.8J Rotary Hammer - Dust Extraction System



5035048628003

Product Description:

Impact Force (E.P.T.A.): T3JR No-load Load (rpm): Ø Wood/Concrete/Metal/Drill Bit (mm): Striking Rate (cps/min): Vibration Level (m/s²): Mode (Rotation/Perforation/Percussion) :Quick-change chuck



Product features and benefits:

- Safety disengagement eliminates the risk of jerks when the Drill Bit Locks Rotation Stop for light chiseling in soft building materials, brick and occasionally in

- Lightweight concrete Ideal for drilling anchor holes from 4 to 22 mm in concrete
- Diameter Dust extraction telescope for optimal suction of concrete dust during drilling Strong mechanism delivers high power and is not stressed
- Reinforced sealing provides maximum protection against dust and ensures good longevity of the tool Rubber-coated rear handle for better comfort
- Electronic variable speed allows for easy control of the tool
- Rounded overall shape for better tool hold Ventilation slots arranged so that no air is blown into the user's eyes

Specifications techniques :

- Capacity (wood):
 - 30 mm
- Power: 800 W
- Drilling Capacity (Metal):
 - 13 mm

Product Warranty:

This product has a 1-year warranty extended to 3 years after registration

Included Items:

- Depth stop (x1)
- D25301D Dust Extraction Telescope (x1)
- Mallette de transport TOUGHSYSTEM® DS150 (x1) Multi-position side handle (x1)

D25135K-QS

SDS-plus 800W 2.8J Rotary Hammer - Dust Extraction System

5035048628003



Product that is part of the D25135K-QS composition

Ref	▲ Title ▼	▲ ▼
D25134-EC	WORKING UNIT 26MM 3 MODE WITH QCC	
D25301D-XJ	DEWALT SDS-plus Hammer Dust Suction Telescope (except D25404/5K)	
MP09620-QZ	DS150 EMPTY FOR KITTING	