

LITHIUM CELL/BATTERY TEST SUMMARY

IN ACCORDANCE WITH SUB-SECTION 38.3
OF MANUAL OF TESTS AND CRITERIA



N/A = Not Applicable

1. Name of cell / battery

YC14650-3711-1S1P 3,7V 1100mAh 4,07Wh Rechargeable Lithium Ion Battery

2. Manufacturer of cell / battery / product

Name	Ansmann AG
Address	Industriestr. 10, 97959 Assamstadt
Phone	+49 6294 4204-0
Email	info@ansmann.de
Website	www.ansmann.de

3. Test laboratory of cell / battery / product

Name	Shanghai Research Institute of Chemical Industry Testing Centre
Address	No.345, Yunling East Road, Shanghai, China
Phone	021-52569800
Email	Mr. Wang 021-52815377-0723 E-mail: wyorama@gmail.com
Website	http://www.ghs.cn

4. ID-number and date

Unique test report identification number	1119010321	Date of test report	23.01.2019
--	------------	---------------------	------------

DESCRIPTION OF CELL / BATTERY

5. Mark the type of cell/battery with an "•"

<input type="radio"/> Lithium ion cell	<input type="radio"/> Lithium metal cell
<input checked="" type="radio"/> Lithium ion battery	<input type="radio"/> Lithium metal battery

6. Parameters

	Cell	Battery
Mass in gram (g):		28
Lithium ion: Indicate watt-hour rating (Wh):		4,07Wh
Lithium metal: Indicate lithium metal content in gram (g):		0,385

7. Physical description of cell / battery

Lithium Ion

LITHIUM CELL/BATTERY TEST SUMMARY

IN ACCORDANCE WITH SUB-SECTION 38.3
OF MANUAL OF TESTS AND CRITERIA



Name of cell/battery (taken from field 1)

YC14650-3711-1S1P 3,7V 1100mAh 4,07Wh Rechargeable Lithium Ion Battery

8. Model numbers

1600-0305; 1600-0100; 1600-0117; 1600-0133; 1600-0133-1; 1600-0164-520

TESTS AND RESULTS

9. List of tests conducted and results - Mark N/A, pass or fail with an "•"	N/A	pass	fail
T1 - Altitude simulation	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T2 - Thermal Test	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T3 - Vibration	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T4 - Shock	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T5 - External Short Circuit	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T6 - Impact / Crush	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T7 - Overcharge	<input checked="" type="radio"/>	<input type="radio"/>	<input type="radio"/>
T8 - Forced Discharge	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
	<input checked="" type="radio"/>	<input type="radio"/>	<input type="radio"/>
	<input checked="" type="radio"/>	<input type="radio"/>	<input type="radio"/>

10. Reference to assembled battery testing requirements

I

N/A

11. Reference to the revised edition of the Manual of Tests and Criteria used and to amendments thereto

ST-SG-AC10-11-Rev6-38.3

12. The manufacture of the cell / battery is in accordance with the documented quality management system as required by the regulations.

13. Place, Date	14. Title, Surname, First name	15. Company stamp and signature
Assamstadt 14.11.2019	Adrian Selke	Selke, Adrian <small>Digital unterschrieben von Selke, Adrian Datum: 2019.11.18 10:45:37 +01'00'</small>