

CK8,0-ED-16,00M AG - Crimp contact



1550050

<https://www.phoenixcontact.com/in/products/1550050>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, contact diameter: 8 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 16 mm² ... 16 mm², AWG 6

Commercial data

Item number	1550050
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BF7
Product key	AF7AIG
GTIN	4067923025455
Weight per piece (including packing)	18.41 g
Weight per piece (excluding packing)	18.41 g
Customs tariff number	85366990
Country of origin	DE

CK8,0-ED-16,00M AG - Crimp contact



1550050

<https://www.phoenixcontact.com/in/products/1550050>

Technical data

Notes

General	for HC-M-...-35 contact carriers
---------	----------------------------------

Mounting

Assembly note	The contacts are qualified for crimping dies in accordance with DIN 46235. Klauke, for example, offers the appropriate tool: Crimping dies from the D22 series are required for the EKM6022 battery-operated hydraulic crimping pliers. Due to the narrow crimping width of 5 mm, it is very important to make two compressions next to one another. For the EK12042 model, crimping dies from the HD13 series are required. Due to a wider crimping process, only one compression is required.
	The quality of a crimp connection is determined by DIN EN 60352-2.

Product properties

Product type	Crimp contact
Series	HC-M-...-35
Type	Individual male contact
Contact material type	turned

Connection data

Contact connection type	Pin
Connection technology	Crimp connection
Conductor cross section	16 mm ² ... 16 mm ²
Connection cross section AWG	6
Stripping length of the individual wire	19 mm
Conductor cross section flexible	16 mm ² ... 16 mm ²

Material specifications

Contact material	Copper alloy, lead-free
Contact surface material	silver-plated

Dimensions

Mechanical characteristics	
Contact diameter	8 mm

Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	≥ 500

Environmental and real-life conditions

CK8,0-ED-16,00M AG - Crimp contact

1550050

<https://www.phoenixcontact.com/in/products/1550050>



Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

CK8,0-ED-16,00M AG - Crimp contact

1550050

<https://www.phoenixcontact.com/in/products/1550050>



Classifications

ECLASS

ECLASS-11.0	27440204
ECLASS-13.0	27440204

ETIM

ETIM 9.0	EC000796
----------	----------

CK8,0-ED-16,00M AG - Crimp contact



1550050

<https://www.phoenixcontact.com/in/products/1550050>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

CK8,0-ED-16,00M AG - Crimp contact

1550050

<https://www.phoenixcontact.com/in/products/1550050>



Accessories

CK8,0-ED-16,00F AG - Crimp contact

1550058

<https://www.phoenixcontact.com/in/products/1550058>



Crimp contact, contact diameter: 8 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 16 mm² ... 16 mm², AWG 6

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in