

ENERGY ABSORBER WITH INTEGRATED FIXE Y LANYARD IN KERNMANTEL ROPE ABS'O EDGE


REF.
NHDYA

neofeu.com

FALL PROTECTION ONLY*
*Un seul métier, l'antichute

REF.
NHDYA XX YY
LG CONNECTORS

CERTIFICATION : EN 355 : 2002 / REGULATION : 2016 / 425
SHEETS : VG11 11.062 / VG11 11.074



A Screw gate connector
ref. NM16NS

Shock absorber

Sewn termination with
sheath and thimble

Polyamide kernmantel
rope Ø 12 mm



r=0,5

REF. : NHDYA10

TESTED
140 KG

REF.

NM16NS

NM24N

NM28N

TECHNICAL SPECIFICATIONS

- Vertical and horizontal use
- Maxi user weight 140 kg
- Energy absorber with a polyamide and polyester tearing strap of 31 mm breadth wrapped with a protective pouch
- Sheathed and braided polyamide rope Ø12 mm
- Arrest force < 600 daN
- Static resistance ≥ 15 kN
- Available length without connectors : 1m
- Weight : 380 g (NHDYA10)

BEWARE OF NECESSARY MINIMUM CLEARANCE. SEE USER MANUAL FOR FURTHER INFORMATION


USE

Works on height with vertical fall hazards. Works in horizontal with fall hazard over a sharp edge (R : 0,5 mm) and with minimum clearance under user's feet (see minimum clearance).

DESCRIPTION

Energy absorber with integrated fixe Y lanyard in kernmantel rope. A removable screw gate connector on energy absorber side and two removable or irremovable connectors on the lanyard side.

MINIMUM CLEARANCE AND FALL FACTORS



MAXIMUM USER WEIGHT 100 KG				
REF.	MAX. LG	MINIMUM CLEARANCE (FACTORS)		
		0	1	2
NHDYA10..	1,3 m	h ≥ 2,75 m	h ≥ 4,05 m	h ≥ 4,30 m
MAXIMUM USER WEIGHT 140 KG				
NHDYA10..	1,3 m	h ≥ 2,75 m	h ≥ 4,05 m	h ≥ 4,90 m
HORIZONTAL USE				
NHDYA10..	1,3 m	h ≥ 5,80 m		