





Product designation			Micro PLC - Base module with RS485 onboard
Product type designation			LRD20RD024P1
Auxiliary supply voltage			24VDC
Number of inputs	n°	8 digital + 4 digital/analog	
Number of outputs	N°	8 relay	
Max I/O number (base module + expansion modules)			20+24
Power supply			
Rated auxil. supply voltage			24VDC
Operating voltage range			20.4...28.8VDC
Avarage current consumption	mA	185	
Power consumption Max	W	5	
Digital inputs			
Number of digital input	n°	8 + 4 digital/analog	
Rated voltage	V	24VDC	
Input signals	State 0 (OFF) State 1 (ON)		<5VDC >15VDC
Response time	0 to 1 (OFF-ON)  1 to 0 (ON-OFF)		4ms (0.5ms for high speed)  4ms (0.3ms for high speed)
Analog inputs			
Number of analog input	n°	4 digital/analog	
Analog input type	Voltage inputs		
Inputs signal range	V	0...10	
Resolution	0.01V		
Bit of conversion	bit	8	
Current consumption at	10VDC	mA	<0.17mA
Input impedance			kΩ >40
Admissible overload			VDC 28
Sampling time	ms		5...20ms(LADDER), 2...10ms (FBD)
Maximum cable lenght	m / ft		≤30m/98ft (shielded wire)
Maximum cable lenght	m / ft		≤30m/98ft (shielded wire)
Digital outputs			
Number of digital output	n°	8	
type	Relay		
type	Relay		
System resources			

Display				LCD display, 4 lines x 16 characters
Display				LCD display, 4 lines x 16 characters
Communications				
Type of communication port				RS485, 2 wire
Connections				
Terminals type				Screw
Tightening torque for terminals				
				max Nm 0.6
				Max lbft 0.4
Conductor section				
AWG/Kcmil				
				min 26
				max 14
IEC				
				min mm² 0.14
				max mm² 2.5
Ambient conditions				
Temperature				
Operating temperature				
				min °C -20
				max °C +55
Storage temperature				
				min °C -40
				max °C +70
Relative humidity				% 20...90% without condensation
Housing				
Mounting				35mm DIN rail or screw fixing (M4x20mm)
Degree of protection				IP20
Dimensions (W x H x D)				mm 126 x 106 x 59.6
Weight				g 360
Dimensions				



### Wiring diagrams



### Certifications and compliance

#### Compliance

CSA C22.2 n° 142

IEC/EN 61131-2

UL508

#### Certificates

cULus

EAC