

Jul.1.2018 Copyright 2018 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case that the application demands a high level of reliability, such as automotive,
 please contact a company representative for further information.

Δ	REVISIONS	BY	CHKD	DATE	Δ	REVISIONS	BY	CHKD	DATE
Δ					Δ				
Δ					Δ				

APPLICABLE STANDARD				
RATING	VOLTAGE	CONTACT No. / ~ *	AC 250 V DC V	APPLICABLE CABLES
	CURRENT	CONTACT No. / ~ *	3 A	IMPEDANCE FREQUENCY RANGE
	POWER			Ω (0 ~ Hz)
	SPECIALTY			OPERATING TEMPERATURE RANGE
				-35℃ ~ +85℃ (Notes:1)

SPECIFICATIONS

No.	ITEM	CONDITIONS	TEST STANDARD	MIN	MAX	UNITS	QT.	AT
1	DESIGN-MATERIAL-FINISH	ADC Applicable Std. and eg 3-160056-01		-	-	-	○	○
2	MARKING			-	-	-	○	○
3	INSULATION RESISTANCE	Must be over standard value at DC 500V.	MIL-STD-1344	1000	-	MΩ	○	-
4	CONTACT RESISTANCE	The voltage drop must be under the Std. value at DC 0.1 A.	MIL-STD-1344	-	30	mΩ	○	-
	UNIT CONTACT CONTACT	The voltage drop must be under the Std. value at DC A.		-	-	mΩ	-	-
5	DIELECTRIC WITHSTANDING VOLTAGE	Must withstand AC eg 650V for one minute.	MIL-STD-1344	-	-	-	○	-
6	LOW LEVEL CIRCUIT	The Contact Resistance must be under the Std. value at DC 20mV less and mA.		-	-	mΩ	-	-
7	DRY CIRCUIT	Must have conductivity in alternate current at DC μV.		-	-	-	-	-
8	CONTACT ENGAGEMENT AND SEPARATION FORCES	Must be suitable for the Std. gauge size value at applicable gauge.		-	-	gf	-	-
	MATING AND UNMATING FORCES	Must be suitable for the Std. value.		-	-	kof	-	-
9	HUMIDITY	Insulation resistance must be over the Std. value at 40±2℃ 90-95% 96 hours. at high humidity after high humidity	MIL-STD-1344	1000	-	MΩ	○	-
10	VIBRATION	Must have no damage, crack and looseness of parts at Frequency range 10-55 Hz, amplitude 0.75mm-G at 2 hours for 3 directions.	MIL-STD-1344	-	-	-	○	-
11	SHOCK	Must have no damage, crack and looseness of parts after 3 cycles at 490 1/2 in 3 directions.	MIL-STD-1344	-	-	-	○	-
12	TEMPERATURE CYCLING	Must have no damage, crack and looseness of parts for -55-185℃ 5 cycles.	MIL-STD-1344	-	-	-	○	-
13	DURABILITY UNIT CONTACT CONTACT	Must be less than the Std. value after 30 insertion and extraction cycles at the condition described in above item No.4.	MIL-STD-1344	-	30	mΩ	○	-
14	SALT SPRAY (CORROSION).	Must not have heavy corrosion after salt water spray for hours.		-	-	-	-	-
15	H ₂ S-EXPOSURE	Must not have heavy corrosion after ppm for hours.		-	-	-	-	-
16	SO ₂ -EXPOSURE	Must not have heavy corrosion after ppm for hours.		-	-	-	-	-

Notes:1
 This temperature includes a rise by heat's generation of connector when electricity passes.

REMARKS	APPROVED	<i>H. Yamamoto</i>	94.3.25	HIROSE ELECTRIC CO., LTD.	ISSUED BY
	REVIEWED				
	CHECKED	<i>J. Oma</i>	94.3.25		
	DESIGNED	<i>M. Gotoh</i>	94.3.24		
	DRAWN	<i>M. Gotoh</i>	94.3.24		
DRAWING NO. SLC4-160056-01				PART NO. DF1B- * DEP-2.5RC	
SPECIFICATION SHEET				CODE No. 0350 9 CL541-0377-5	

TO

