

DIN 41612 SIGNAL HEADERS & RECEPTACLES

COST-EFFECTIVE YET DURABLE CONNECTORS

AFCI offers a broad and complete range of interconnection systems conforming to DIN 41612 and IEC 603-2 specifications. They are easily available, cost-effective, highly durable and ideal for Industrial, Telecom and Data markets.

- Standard Mount and Reverse Mount options available
- Available up to 3 rows and 96 positions with Solder, Press-fit and pin-in Paste terminations
- Revolutionary beam-on-beam contact interface
- 3 standard performance class options available



FEATURES

- 2.54mm pitch
- Modular system
- Selective loading pattern for contacts
- FMLB/LMEB contacts
- Wide range of accessories (board-locks, latches, shrouds, hoods, keys)
- Rear plug up variants in press-fit applications

BENEFITS

- Adequate spacing for routing PCB traces
- Standardized and cost-effective solutions
- Improve creepage distance, allow custom loading
- Critical grounding option
- Enhances the connector suitability and flexibility
- Extended mating applications via shrouds on the rear side of the PCB

TECHNICAL INFORMATION

MATERIALS

- Insulator: Polyester Thermoplastic
- Housings can withstand exposure to lead free wave soldering temperature of 260°C to 265°C when used along with high temperature adhesive or protective metallic device for right angle connectors.
- Contact: Copper Alloy (Male & Female contact)
- Plating: Lead-free version
- Male & Female contacts (DIN 41612 compliant)
- Active contact areas selectively plated
- Gold over Nickel or GXT® over Nickel on mating surface
- Tin over Nickel on solder termination

MECHANICAL PERFORMANCE

- Mating Insertion Force per Contact: ≤ 0.94N
- Mating Extraction Force per Contact: ≥ 0.15N
- Contact Retention in Insulator: ≥ 20N
- Vibration: ≤ 1μs
 - \leq 40m Ω
- Shock: ≤ 1μs
 - \leq 40m Ω

APPROVALS AND CERTIFICATIONS

Approved by UL to both UL and CSA standards

PACKAGING

- Tray
- Tube
- Carton

ELECTRICAL PERFORMANCE

- Current Rating at 20°C: 1.5A
- Maximum Current: 2A
- Contact Resistance: ≤ 20mΩ
- Insulation Resistance: $\geq 10^6 M\Omega$
- Test Voltage (rms): 1000V
- Creepage and Clearance Distance: ≥ 1.2mm
- Wiping/Plug-in Direction: ≥ 1.8mm

ENVIRONMENTAL

- Temperature Range: -55°C to +125°C
- Damp Heat
- Steady state 56 days: Class 1
- Steady state 21 days: Class 2
- Not applicable: Class 3

SPECIFICATIONS

- DIN 41612
- IEC 603-2

TARGET MARKETS/APPLICATIONS



Switching/Routing Enterprise Transmission Access - wired/wireless



Home Entertainment White Goods Phones



Servers Personal Computing Peripheral Device



Medical
Lighting
Process Control
Transportation
Instrumentation
Vehicle Electronics
Energy Transmission/Distribution Control

PART NUMBERS

Style	Connector	Configuration	Rows Loaded	Termination	Part Numbers
С	Right Angle Header	2 row / 64 pos.	a & c	Solder-to-board	860946471137*5ELF
				Press-fit	860946471947*5E1LF
		3 row / 96 pos.	a, b, c	Solder-to-board	860939671137*5ELF
				Press-fit	860939671947*5E1LF
	Straight Receptacle	2 row / 64 pos.	a & c	Solder-to-board	860946481147*5V1LF
				Press-fit	860946481947*5E3LF
		3 row / 96 pos.	a, b, c	Solder-to-board	860939681147*5V1LF
				Press-fit	860939681947*5E3LF
C/2	Right Angle Header	2 row / 32 pos.	a & c	Solder-to-board	860943273137*5ELF
		3 row / 48 pos.	a, b, c		860934873137*5ELF
	Straight Receptacle	2 row / 32 pos.	a & c		860943283147*5V1LF
		3 row / 48 pos.	a, b, c	Solder-to-board	860934883147*5V1LF
				Press-fit	860934883947*5E3LF
В	Right Angle Header	1 row / 32 pos.	a only	Solder-to-board	860913251137*5ELF
		2 row / 64 pos.	a & b		860926451137*5ELF
	Straight Receptacle	1 row / 32 pos.	a only		860913261147*5V1LF
		2 row / 64 pos.	a & b		860926461147*5V1LF
B/2	Right Angle Header			Solder-to-board	860923253137*5ELF
	Straight Receptacle	2 row / 32 pos.	a & b		860923263147*5E1LF
R	Straight Header	2 row / 64 pos.	a & c	Solder-to-board	860946478147*5ELF
				Press-fit	860946478947*5E1LF
		3 row / 96 pos.	a, b, c	Solder-to-board	860939678147*5ELF
				Press-fit	860939678947*5E1LF
	Right Angle Receptacle	2 row / 64 pos.	a & c	Solder-to-board	860946488137*5V1LF
				Press-fit	860946488947*5E3LF
		3 row / 96 pos.	a, b, c	Solder-to-board	860939688137*5V1LF
				Press-fit	860939688947*5E3LF
R/2	Straight Header	2 row / 32 pos.	a & c	Solder-to-board	860943276147*5ELF
		3 row / 48 pos.	a, b, c	Solder-to-board	860934876147*5ELF
				Press-fit	860934876947*5E1LF
	Right Angle Receptacle	2 row / 32 pos.	a & c	Solder-to-board	860943286137*5E1LF
		3 row / 48 pos.	a, b, c		860934886137*5E1LF
Q	Straight Header	2 row / 64 pos.	a & b	Solder-to-board	860926458147*5ELF

Notes

Asterisk (*) in part number denotes Performance class: PN Code 6,5,4 for Class 1, 2 & 3 respectively. Custom loading and other options available on request.