



Switches > Toggle Switches



Contact Current Rating: 3 A

Configuration (Pole-Throw): Double Pole - Double Throw

Operating Function: On On

Number of Positions: 2

Operating Voltage: 28 VDC

Features

Product Type Features

Sealed Device	Yes
Switch Type	Rocker Switch

Configuration Features

Configuration (Pole-Throw)	Double Pole - Double Throw
Operating Function	On On
Number of Positions	2

Electrical Characteristics

Contact Current Rating	3 A
Operating Voltage	125 VAC

Body Features

Product Orientation	Right Angle
---------------------	-------------

Contact Features

Switch Contact Plating Material	Silver
---------------------------------	--------

Termination Features

Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------

Mechanical Attachment

Product Mount Type	Board Mount
--------------------	-------------



Housing Features

Process Sealed	No
----------------	----

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (4% in Component Part) <b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 260°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 2267074-1  
[PMS9P1B05M2RE](#)



TE Part # 2267074-3  
[PMS9P1B05M2QE](#)



TE Part # 2267076-3  
[PMS8P1B09M2RE](#)



TE Part # 2267074-4  
[PMS9P1B05M2QE](#)




Customers Also Bought



TE Part #640250-4

04P SL156 HSG W/LCK RAMP NATL



TE Part #9-1618384-6

LEV200AOANA = RELAY, LEV200 SPST-NO



TE Part #1571987-2

A201J1AQ004=DBL POLE, ROCKER

Documents

Product Drawings

RMD1R102M6QES

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2267087-4\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_2267087-4\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_2267087-4\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Subminiature Switches

English