



**Part Number: 9860**

Twinax 124Ω, 1 Pr #16 Sol BC, PO Ins, OA DF+TC Brd, PVC Jkt, CMX

[📦 Request Sample](#)

## Product Description

Twinax 124Ω, 1 Pair 16AWG (Solid) Bare Copper, PO Insulation, Overall Duofoil®+Tinned Copper Braid(90%) Shield, PVC Outer Jacket, CMX

## Technical Specifications

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Pairs
16	Solid	BC - Bare Copper	0.051 in	1

Conductor Count:	2
Conductor Size:	16 AWG

#### Insulation

Material	Nominal Diameter
FPE - Foamed Polyethylene	0.161 in

#### Color Chart

Number	Color
1	Blue & Clear

#### Outer Shield Material

Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Aluminum/Polyester/Aluminum	Duofoil®	100 %
Braid	2	TC - Tinned Copper		90 %

#### Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.44 in	0.045 in

### Construction and Dimensions

#### Stranding

Diameter
0.322 mm

### Electrical Characteristics

#### Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR	Outer Conductor DCR
4.2 Ohm/1000ft	1.3 Ohm/1000ft	1.3 Ohm/1000ft

#### Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield	Nom. Capacitance Conductor to Shield
10.9 pF/ft	19.3 pF/ft	10.9 pF/ft

#### Inductance

Element	Nominal Inductance
(Loop)	(Loop) 0.24 µH/ft

#### Impedance

Nominal Characteristic Impedance
124 Ohm

#### High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.2 dB/100m
10 MHz	0.7 dB/100m
50 MHz	1.8 dB/100m
100 MHz	2.9 dB/100m
200 MHz	4.1 dB/100m
400 MHz	6.2 dB/100m

#### Delay

Max. Delay Skew	Nominal Delay	Nominal Velocity of Propagation (VP) [%]
78 ns/100m	1.3 ns/ft	78 %

#### High Freq

Frequency [MHz]
1 MHz
10 MHz
50 MHz
100 MHz
200 MHz
400 MHz

#### Voltage

UL Voltage Rating	Voltage Rating [V]
type CM: 300 V RMS	AWM style 2448: 30 V RMS
300 (CMX) V RMS	

#### Temperature Range

UL Temp Rating:	60°C
Operating Temp Range:	-20°C To +60°C

#### Mechanical Characteristics

Bulk Cable Weight:	98 lbs/1000ft
Max Recommended Pulling Tension:	73 lbs
Min Bend Radius/Minor Axis:	4.5 in

#### Standards

NEC Articles:	800
NEC/(UL) Specification:	CMX
CEC/C(UL) Specification:	CMX
UL AWM Style:	2448

#### Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

#### Flammability, LSOH, Toxicity Testing

UL Flammability:	VW-1
UL voltage rating:	300 V RMS (CM)

**Plenum/Non-Plenum**

Plenum (Y/N):	No
---------------	----

**Part Number**

**Variants**

Item #	Color	Footnote
9860 0101000	Black	C
9860 0102000	Black	C
9860 010500	Black	C

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2019 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.