

# WT-HT HF 2,5X98 BK - Cable tie



3240781

<https://www.phoenixcontact.com/gb/products/3240781>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable binders for quick and secure bundling, heat stabilized to 125°C (also up to 145°C for brief periods)

## Commercial data

Item number	3240781
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BE7131
Product key	BE7131
Catalog page	Page 617 (C-3-2019)
GTIN	4046356704991
Weight per piece (including packing)	0.313 g
Weight per piece (excluding packing)	0.282 g
Customs tariff number	39269097
Country of origin	HR

# WT-HT HF 2,5X98 BK - Cable tie



3240781

<https://www.phoenixcontact.com/gb/products/3240781>

## Technical data

### Product properties

Product type	Cable tie
Type	Internal teeth
Tensile strength GRP	80 N

### Dimensions

Width	2.5 mm
Length	98 mm

### Material specifications

Color	black (RAL 9005)
Material	PA 6.6
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

### Cable/line

External cable diameter	1 mm ... 21 mm
Tensile strength	80 N

### Environmental and real-life conditions

#### Ambient conditions

Optimum ambient temperature (storage/transport)	23.00 °C 50.00 % Polyamide 6.6 has pronounced hygroscopic properties. It absorbs or releases water in accordance with the level of humidity within its environment. Its properties are ideal when the percentage of water is 2 - 3%. The packaging, which is tailored specifically to the product concerned, contains the optimum level of moisture. To ensure that the ideal properties are maintained, the following points should be observed during storage: Keep product stored inside sealed original packaging, carry out any product processing soon after breaking open the packaging, avoid direct sunlight, avoid direct heat.
Ambient temperature (operation)	-40 °C ... 125 °C
Ambient temperature (assembly)	-10 °C ... 60 °C
Resistance to UV radiation	no
Short-term temperature	145 °C

### Mounting

Mounting type	Cannot be removed
---------------	-------------------

# WT-HT HF 2,5X98 BK - Cable tie



3240781

<https://www.phoenixcontact.com/gb/products/3240781>

## Classifications

### ECLASS

ECLASS-13.0	27140702
-------------	----------

### ETIM

ETIM 9.0	EC000046
----------	----------

### UNSPSC

UNSPSC 21.0	39121700
-------------	----------

# WT-HT HF 2,5X98 BK - Cable tie



3240781

<https://www.phoenixcontact.com/gb/products/3240781>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)