






Pin Headers 90° 3.81 mm pitch



linear dimension(Tolerances Standard GB/T 14486-2008)								—	▯	⊥
variable range	to 6	over 6 to 10	over 10 to 30	over 30 to 60	over 60 to 100	over 100 to 160	over 160 to	to 10	over 10 to 100	over 100 to
tolerance	±0.20	±0.30	±0.50	±0.70	±1.00	±1.30	±1.60	0.10	0.30	0.60

Technical Data			
Use Group	B	C	D
Rated Voltage [V]	300	-	300
Rated Current [A]	8	-	8
Wire Range Solid/Stranded [AWG]	-		
Withstanding Voltage	1600V/1Min		
IEC Technical Data			
Overvoltage Category	III	III	II
Contamination Class	3	2	2
Rated Voltage [V]	160	160	250
Rated Current [A]	7	7	7
Impulse withstand voltage [KV]	2.5	2.5	2.5
Conductor cross section Solid/ flexible [mm²]	-		
Material			
Insulation Material	PA66		
Imflammability	UL94V-0		
Contact Material	Copper alloy		
Contactive Coating	Sn Plated		
Other Data			
Pitch / Poles [mm] / [P]	3.81 / 02~24		
Stripping Length [mm]	-		
Screw / Torque(Max) [N.m]	-		
Operating temperature [°C]	-40~105		
Soldering temperature	250°C/5S		
Pin Dimensions [mm]	0.8*0.8		
PCB Hole Diameter [mm]	Ø1.4		