

# PTFIX 6/12X2,5 BU-EX - Distribution block



1221425

<https://www.phoenixcontact.com/gb/products/1221425>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Distribution block, Ex e-certified basic terminal block with feed-in, mounting type: for snapping onto a DIN rail adapter, Direct mounting with flange, Free-hanging, color: blue

## Your advantages

- Ex e certified
- Flexible use, thanks to DIN rail mounting, direct mounting or adhesive mounting
- Clear wiring, thanks to eleven different color variants
- Time-saving conductor connection, thanks to tool-free Push-in direct connection technology
- Time savings of up to 80 %, thanks to ready-to-mount blocks without manual bridging
- Space savings of up to 50 % on the DIN rail, thanks to transverse mounting

## Commercial data

Item number	1221425
Packing unit	8 pc
Minimum order quantity	8 pc
Sales key	BEA123
Product key	BEA123
GTIN	4063151309626
Weight per piece (including packing)	30.637 g
Weight per piece (excluding packing)	21.96 g
Country of origin	PL

# PTFIX 6/12X2,5 BU-EX - Distribution block



1221425

<https://www.phoenixcontact.com/gb/products/1221425>

## Technical data

### Notes

Notes on operation	the blocks can be bridged with one another via the conductor shaft, for corresponding plug-in bridges, see accessories
--------------------	--

### General

Note	The maximum load current of a single clamping unit must not be exceeded.  For power distribution applications, IEC 60364-4-43:2008; modified + corrigendum Okt. 2008 (DIN VDE 0100-430:2010-10) section 433.2 ff must be observed!
------	--

### Product properties

Product type	Distributor terminal block
Number of rows	1
Potentials	1

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Electrical properties

Rated surge voltage	6 kV
Maximum power dissipation for nominal condition	0.77 W

### Connection data

Stripping length	8 mm ... 10 mm
------------------	----------------

### Ex data

#### Rated data (ATEX/IECEx)

Identification	Ⓔ II 2 G Ex eb IIC Gb
Operating temperature range	-60 °C ... 110 °C
Ex-certified accessories	3274054 PTFIX-NS35
	3274056 PTFIX-NS35A
	3274057 PTFIX-NS35A-FIX
	3274058 PTFIX-NS15A
	3274059 PTFIX-NS15A-FIX
	3274060 PTFIX-F
	3022263 CLIPFIX 15
	3022276 CLIPFIX 35-5
	3022218 CLIPFIX 35
List of bridges	1204517 SZF 1-0,6X3,5
	Plug-in bridge / FBS 2-5 / 3030161
	Bridge data
Bridge data	23 A (10 mm <sup>2</sup> )

# PTFIX 6/12X2,5 BU-EX - Distribution block



1221425

<https://www.phoenixcontact.com/gb/products/1221425>

Ex temperature increase	40 K (40 A / 6 mm <sup>2</sup> )
Rated insulation voltage when mounting on DIN rails	400 V
Rated insulation voltage when directly mounted on mounting surface	400 V
output	(Permanent)

## Ex level General

Rated voltage when mounting on DIN rails	440 V
Rated voltage during direct mounting on mounting surface	440 V
Maximum total current	55 A (10 mm <sup>2</sup> )
output	(Permanent)

## Ex level Terminal point

Rated current	22.5 A (2.5 mm <sup>2</sup> )
Maximum load current	27 A (4 mm <sup>2</sup> )
Contact resistance	0.5 mΩ

## Ex connection data Terminal point

Stripping length	8 mm ... 10 mm
Nominal cross section	2.5 mm <sup>2</sup>
Rated cross section AWG	14
Connection capacity rigid	0.14 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Connection capacity AWG	26 ... 12
Connection capacity flexible	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Connection capacity AWG	26 ... 14
output	(Permanent)

## Ex level Feed-in contact

Rated current	40 A (6 mm <sup>2</sup> )
Maximum load current	55 A (10 mm <sup>2</sup> )
Contact resistance	0.2 mΩ

## Ex connection data Feed-in contact

Stripping length	10 mm ... 12 mm
Nominal cross section	6 mm <sup>2</sup>
Rated cross section AWG	10
Connection capacity rigid	0.5 mm <sup>2</sup> ... 10 mm <sup>2</sup>
Connection capacity AWG	20 ... 8
Connection capacity flexible	0.5 mm <sup>2</sup> ... 10 mm <sup>2</sup>
Connection capacity AWG	20 ... 8

## Dimensions

Width	41 mm
Height	28.6 mm
Depth	21.7 mm

## Material specifications

# PTFIX 6/12X2,5 BU-EX - Distribution block



1221425

<https://www.phoenixcontact.com/gb/products/1221425>

Color	blue (RAL 5015)
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA

## Mechanical properties

### Mechanical data

Open side panel	No
-----------------	----

## Environmental and real-life conditions

### Ambient conditions


Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

## Mounting

Mounting type	for snapping onto a DIN rail adapter
	Direct mounting with flange
	Free-hanging

## Drawings

Circuit diagram



# PTFIX 6/12X2,5 BU-EX - Distribution block



1221425

<https://www.phoenixcontact.com/gb/products/1221425>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1221425>



**IECEx**

Approval ID: IECExSEV21.0023U



**ATEX**

Approval ID: SEV21ATEX0557U



**CCC**

Approval ID: 2022122313115884



**UKCA-EX**

Approval ID: CML 22UKEX3672U

# PTFIX 6/12X2,5 BU-EX - Distribution block



1221425

<https://www.phoenixcontact.com/gb/products/1221425>

## Classifications

### ECLASS

ECLASS-13.0	27250118
-------------	----------

### ETIM

ETIM 9.0	EC000897
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# PTFIX 6/12X2,5 BU-EX - Distribution block



1221425

<https://www.phoenixcontact.com/gb/products/1221425>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)