

FEATURES

- **Abrasion Resistant:** Ensures longevity and durability in demanding environments
- **Chemical Resistant:** Suitable for use with various chemicals, enhancing versatility
- **Moisture Resistant:** Prevents degradation from moisture exposure, extending service life
- **Maximum Operating Pressure of 14 bar:** Supports high-pressure applications
- **Wide Temperature Range (-30°C to 60°C):** Suitable for diverse environmental conditions
- **Nylon 12 Material:** Offers flexibility and strength for reliable performance

RS PRO 9.5 mm Flexible Tubing, Nylon 12

RS Stock No: 631-950



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flexible tubing is designed for a variety of industrial applications, offering durability and reliability. Made from high-quality Nylon 12, it is ideal for use in environments requiring abrasion, chemical, and moisture resistance. With a 9.5 mm inside diameter and a 30 m length, this tubing is perfect for air brake systems, food production lines, and more.

General Specifications

Application	Air Brake, Food Production Line, Fuel, Lubrication, Pneumatic
Colour	Black
Material	Nylon 12
Maximum Operating Pressure	14 bar
Number of Tubes	1
Product Type	Flexible Tubing
Resistance Features	Abrasion Resistant, Chemical Resistant, Moisture Resistant

Mechanical Specifications

Inside Diameter	9.5 mm
Length	30 m
Outside Diameter	12 mm

Operation Environment Specifications

Maximum Operating Temperature	60 °C
Minimum Operating Temperature	-30 °C

Approvals

Standards/Approvals	BS 5409, DIN 73378, DIN 74324, ISO 7628, RoHS 3
---------------------	---