


## 1" straight impact wrench - long anvil - high performance



### Description:

- Dual hammer mechanism for tool durability.
- 2 stage trigger for improved control.
- Two forward, two reverse speeds.
- Rubber over molded grip insulating against cold and vibrations.
- Rubber bumper protecting the motor housing.
- 360° adjustable handle for improved comfort.
- Ring retainer hole to use a safety pin.
- Exhaust blows air away from the operator for comfort of use.



	Height H [mm]	Length L [mm]	Length L1 [mm]	Torque NM. [Nm]	Vibration Level [m/s <sup>2</sup> ]	Maximum Speed [rpm]	Weight [Kg]
<b>NM.3030LF</b>	97.0	493.0	101.0	3390.0	15,6 (K=2,05)	5000.0	9.0