

PTS641 Series

SMT Top Actuated Switches



- Features/Benefits**
 - 6.3 x 6.3 mm footprint
 - Multiple heights
 - Ground pin option
- Typical Applications**
 - Metering
 - White goods
 - Home and garden equipment

Specification

FUNCTION: Momentary action
CONTACT ARRANGEMENT: 1 make contact = SPST N.O.
TERMINALS: G type for SMT

Mechanical

TRAVEL:
 0.20 mm ±0.15 mm for 160 &250 gf
 0.30 mm ±0.15 mm for 320 gf
 OPERATING LIFE: 100,000 cycles
 OPERATION FORCE:
 160 gf ±50 gf blue actuator
 250 gf ±50 gf red actuator
 320 gf ±80 gf black actuator

Packaging

Switches in reels of 1,500 pieces.
Dimensions of reels according to EIA 481B
External diameter 330 mm

Electrical

MAXIMUM VOLTAGE: 12 VDC
MAXIMUM CURRENT DC: 50 mA
DIELECTRIC STRENGTH: 250 VA C (1mn)
CONTACT RESISTANCE: 100 m Ω
INSULATION RESISTANCE: ≥ 100 M Ω
BOUNCE TIME: < 5 ms

Environmental

OPERATING TEMPERATURE: -20°C to 85°C


Process

SOLDERING: This component is suited to the following methods:
Infrared Reflow Soldering in accordance with IEC61760-1

NOTE: Specifications listed above are for switches with standard options.
For information on specific and custom switches, consult Customer Service Center.

How To Order


Our easy build-a-switch concept allows you to mix and match options to create the switch you need. To order, select desired option from each category and and place it in the appropriate box.



PTS641 Series

SMT Top Actuated Switches

NO GROUND PIN H = 2.5, 3.1, or 3.4 mm



GROUND PIN H = 2.5, 3.1, or 3.4 mm

