

SIMATIC Compact Field Unit CIO HART edition with 16x freely configurable channels (AI; AQ; HART; DI 24 V DC; DI NAMUR; DQ 24 V DC 0.5/2 A; counter) installation up to hazardous zone 2 channel diagnostics PROFINET interface, use of PROFINET BusAdapter Configuration in Run (CiR) media redundancy (MRP) PROFINET system redundancy (S2) temperature range -40 to +70 °C conformal coating mounting on 35 mm DIN rail



| General information | |
|---|---|
| Product type designation | CFU CIO HART |
| HW functional status | FS01 |
| Firmware version | V1.0 |
| <ul style="list-style-type: none"> FW update possible | Yes |
| Vendor identification (VendorID) | 002AH |
| Device identifier (DeviceID) | 0319H |
| Number of channels | 16 |
| Product function | |
| <ul style="list-style-type: none"> I&M data | Yes; I&M0 to I&M3 |
| <ul style="list-style-type: none"> Isochronous mode | No |
| <ul style="list-style-type: none"> The user can configure digital channels as input/output as required | Yes |
| <ul style="list-style-type: none"> Digital channels can be parameterized | Yes |
| Engineering with | |
| <ul style="list-style-type: none"> STEP 7 TIA Portal configurable/integrated from version | V19 Update 2 |
| <ul style="list-style-type: none"> STEP 7 configurable/integrated from version | STEP 7 V5.7.1.4 |
| <ul style="list-style-type: none"> PCS 7 configurable/integrated from version | V9.1 SP2 UC7 (+PDM V9.3 Upd1) |
| <ul style="list-style-type: none"> PROFIBUS from GSD version/GSD revision | - / - |
| <ul style="list-style-type: none"> PROFINET from GSD version/GSD revision | GSDML V2.43 2024.03.04 |
| Operating mode | |
| <ul style="list-style-type: none"> DI | Yes |
| <ul style="list-style-type: none"> Counter | Yes |
| <ul style="list-style-type: none"> DQ | Yes |
| CiR - Configuration in RUN | |
| Reparameterization possible in RUN | Yes |
| Installation type/mounting | |
| Mounting | on 35 mm DIN rail, 2 spacing units wide |
| Mounting position | Horizontal, vertical |
| Recommended mounting position | horizontal set up |
| Supply voltage | |
| Type of supply voltage | 24 V DC |
| Rated value (DC) | 24 V |
| permissible range, lower limit (DC) | 19.2 V |
| permissible range, upper limit (DC) | 28.8 V |
| Reverse polarity protection | Yes |
| Short-circuit protection | Yes |
| Redundant power supply | Yes |
| Mains buffering | |

| | |
|--|--|
| <ul style="list-style-type: none"> • Mains/voltage failure stored energy time | 1 ms; For communication |
| Input current | |
| Current consumption (rated value) | 4.1 A; RJ45 BusAdapter, 8xDI, 4xAI, 2xAQ, 2xDQ with 2 A each |
| Current consumption, max. | 9 A |
| Inrush current, max. | 7 A |
| I ² t | 0.5 A ² ·s |
| Encoder supply | |
| Number of outputs | 16 |
| Output voltage, min. | 12 V |
| Short-circuit protection | Yes; Electronic |
| Output current | |
| <ul style="list-style-type: none"> • up to 60 °C, max. | 8 A; total current DQ + additional current for analog channels |
| <ul style="list-style-type: none"> • up to 70 °C, max. | 6 A; total current DQ + additional current for analog channels |
| Power loss | |
| Power loss, typ. | 6.6 W; RJ45 BusAdapter, 8xDI, 4xAI, 2xAQ, 2xDQ with 12 ohms load each |
| Address area | |
| Address space per station | |
| <ul style="list-style-type: none"> • Address space per station, max. | 1 440 byte; Dependent on configuration |
| Digital inputs | |
| Number of digital inputs | 16 |
| Digital inputs, parameterizable | Yes |
| Sourcing/sinking input | Yes |
| Input characteristic curve in accordance with IEC 61131, type 1 | Yes |
| Input characteristic curve in accordance with IEC 61131, type 2 | No |
| Input characteristic curve in accordance with IEC 61131, type 3 | Yes |
| Pulse extension | Yes; off, 50 ms, 100 ms, 200 ms, 500 ms, 1 s, 2 s |
| Digital input functions, parameterizable | |
| <ul style="list-style-type: none"> • Gate start/stop | Yes; hardware gate, usable by multiple DI counters |
| <ul style="list-style-type: none"> • Freely usable digital input | Yes; Parameterizable input filter |
| <ul style="list-style-type: none"> • Counter | Yes |
| <ul style="list-style-type: none"> — Number, max. | 16 |
| <ul style="list-style-type: none"> — Counting frequency, max. | 5 kHz; high-speed counter mode, sinking input; 1 kHz for sourcing input, NAMUR |
| <ul style="list-style-type: none"> — Counting width | 32 bit |
| <ul style="list-style-type: none"> — Counting direction up/down | Yes; Up |
| Input voltage | |
| <ul style="list-style-type: none"> • Rated value (DC) | 24 V |
| <ul style="list-style-type: none"> • for signal "0" | -9 V to +5 V |
| <ul style="list-style-type: none"> • for signal "1" | +11 to +30V |
| <ul style="list-style-type: none"> • permissible voltage at input, min. | -9 V |
| <ul style="list-style-type: none"> • permissible voltage at input, max. | 30 V |
| Input current | |
| <ul style="list-style-type: none"> • for signal "1", typ. | 2.5 mA; max: 2.5 mA sourcing input; 2.3 mA sinking input; 10 mA fast counter; 6.5 mA NAMUR |
| Input delay (for rated value of input voltage) | |
| for standard inputs | |
| <ul style="list-style-type: none"> — parameterizable | Yes; none / 0.05 / 0.1 / 0.2 / 0.4 / 0.8 / 1.6 / 3.2 / 12.8 / 20 ms |
| Cable length | |
| <ul style="list-style-type: none"> • shielded, max. | 1 000 m |
| <ul style="list-style-type: none"> • unshielded, max. | 600 m |
| Digital outputs | |
| Type of digital output | Transistor |
| Number of digital outputs | 16 |
| Current-sinking | No |
| Current-sourcing | Yes |
| Short-circuit protection | Yes |
| <ul style="list-style-type: none"> • Response threshold, typ. | 4.1 A |
| Open-circuit detection | Yes |
| Overload protection | Yes |

| | |
|--|--|
| Limitation of inductive shutdown voltage to | typ. L+ (-11 V) |
| Controlling a digital input | Yes |
| Switching capacity of the outputs | |
| • with resistive load, max. | 2 A |
| • on lamp load, max. | 5 W |
| Load resistance range | |
| • lower limit | 12 Ω |
| • upper limit | 12 k Ω |
| Output voltage | |
| • Type of output voltage | DC |
| • for signal "1", min. | Ue minus 1 V |
| Output current | |
| • for signal "1" rated value | 2 A |
| • for signal "0" residual current, max. | 0.1 mA |
| Output delay with resistive load | |
| • "0" to "1", typ. | 50 μ s |
| • "0" to "1", max. | 100 μ s |
| • "1" to "0", typ. | 50 μ s |
| • "1" to "0", max. | 100 μ s |
| Parallel switching of two outputs | |
| • for uprating | No |
| • for redundant control of a load | No |
| Switching frequency | |
| • with resistive load, max. | 100 Hz |
| • with inductive load, max. | 1 Hz; at 2 A; 2 Hz at 0.5 A |
| • on lamp load, max. | 10 Hz |
| Total current of the outputs | |
| • Current per channel, max. | 2 A |
| horizontal installation | |
| — up to 60 °C, max. | 8 A |
| — up to 70 °C, max. | 6 A |
| vertical installation | |
| — up to 60 °C, max. | 8 A |
| — up to 70 °C, max. | 6 A |
| Cable length | |
| • shielded, max. | 1 000 m |
| • unshielded, max. | 600 m |
| Analog inputs | |
| Number of analog inputs | 16 |
| Input ranges (rated values), currents | |
| • 0 to 20 mA | Yes; 16 bit incl. sign |
| — Input resistance (0 to 20 mA) | 233 Ω |
| • 4 mA to 20 mA | Yes; 16 bit incl. sign |
| — Input resistance (4 mA to 20 mA) | 233 Ω |
| HART communication | |
| • Primary Master | Yes |
| • input resistance (with HART communication) | 233 Ω |
| Cable length | |
| • shielded, max. | 1 000 m |
| • unshielded, max. | 600 m |
| Analog outputs | |
| Number of analog outputs | 16; short-circuit proof with respect to ground |
| Current output, no-load voltage, max. | 24 V |
| Output ranges, current | |
| • 0 to 20 mA | Yes; 15 bit |
| • -20 mA to +20 mA | No |
| • 4 mA to 20 mA | Yes; 16 bit incl. sign |
| Connection of actuators | |
| • for current output two-wire connection | Yes |

| | |
|--|---|
| Load impedance (in rated range of output) | |
| • for current outputs, min. | 50 Ω |
| • with current outputs, max. | 750 Ω |
| • with current outputs, inductive load, max. | 10 mH |
| Destruction limits against externally applied voltages and currents | |
| • Voltages at the outputs | 36 V; Minus 0.3 V lower limit |
| Cable length | |
| • shielded, max. | 1 000 m |
| • unshielded, max. | 600 m |
| Analog value generation for the inputs | |
| Measurement principle | integrating (Sigma-Delta) |
| Integration and conversion time/resolution per channel | |
| • Resolution with overrange (bit including sign), max. | 16 bit |
| • Integration time, parameterizable | Yes; channel by channel |
| Smoothing of measured values | |
| • parameterizable | Yes; none, weak, medium, strong, channel-by-channel |
| Analog value generation for the outputs | |
| Settling time | |
| • for resistive load | 2 ms; 750 ohm |
| • for inductive load | 1.2 ms |
| Encoder | |
| Connection of signal encoders | |
| • for current measurement as 2-wire transducer | Yes |
| Connectable encoders | |
| • NAMUR encoder/changeover contact according to EN 60947 | Yes; no CO contact |
| • 2-wire sensor | Yes |
| — permissible quiescent current (2-wire sensor), max. | 1.5 mA |
| Errors/accuracies | |
| Linearity error (relative to input range), (+/-) | 0.05 % |
| Temperature error (relative to input range), (+/-) | 0.005 %/K |
| Crosstalk between the inputs, min. | 60 dB |
| Repeat accuracy in steady state at 25 °C (relative to input range), (+/-) | 0.05 % |
| Linearity error (relative to output range), (+/-) | 0.02 % |
| Temperature error (relative to output range), (+/-) | 0.003 %/K |
| Crosstalk between the outputs, min. | 70 dB |
| Repeat accuracy in steady state at 25 °C (relative to output range), (+/-) | 0.02 % |
| Operational error limit in overall temperature range | |
| • Current, relative to input range, (+/-) | 0.5 % |
| • Current, relative to output range, (+/-) | 0.5 %; 0 ... 60 °C: 0.2 % |
| Basic error limit (operational limit at 25 °C) | |
| • Current, relative to input range, (+/-) | 0.1 % |
| • Current, relative to output range, (+/-) | 0.1 % |
| Interfaces | |
| Number of PROFINET interfaces | 1 |
| 1. Interface | |
| Interface type | PROFINET |
| Isolated | Yes |
| Interface types | |
| • Number of ports | 2; via BusAdapter |
| • integrated switch | Yes |
| • BusAdapter (PROFINET) | Yes |
| Protocols | |
| • PROFINET IO Device | Yes |
| • Media redundancy | Yes; as MRP client |
| Interface types | |
| RJ 45 (Ethernet) | |

| | |
|--|---|
| • 100 Mbps | Yes |
| • Autonegotiation | Yes |
| • Autocrossing | Yes |
| Protocols | |
| Supports protocol for PROFINET IO | Yes |
| HART protocol | Yes |
| • Protocol version | up to Revision 7 |
| PROFINET IO Device | |
| Services | |
| — Shared device | No |
| Redundancy mode | |
| • PROFINET system redundancy (S2) | Yes; Type S2 |
| Media redundancy | |
| — MRP | Yes |
| Open IE communication | |
| • LLDP | Yes |
| Interrupts/diagnostics/status information | |
| Status indicator | Yes |
| Alarms | Yes |
| Diagnostics function | Yes |
| Substitute values connectable | Yes |
| Alarms | |
| • Diagnostic alarm | Yes |
| • Maintenance interrupt | Yes |
| • Limit value alarm | Yes |
| • Hardware interrupt | Yes |
| Diagnoses | |
| • Monitoring the supply voltage | Yes |
| • Wire-break | Yes; channel by channel |
| • Short-circuit | Yes; channel by channel |
| • Group error | Yes |
| • Overflow/underflow | Yes; channel by channel |
| Diagnostics indication LED | |
| • RUN LED | Yes; green LED |
| • ERROR LED | Yes; red LED |
| • MAINT LED | Yes; Yellow LED |
| • Monitoring of the supply voltage (PWR-LED) | Yes; green/red LED |
| • Channel status display | Yes; green/red LED |
| • Status indicator digital input (green) | Yes |
| • Status indicator digital output (green) | Yes |
| • Connection display LINK TX/RX | Yes; 2x green link LEDs on BusAdapter |
| Integrated Functions | |
| Frequency measurement | Yes |
| • Number of frequency meters | 16 |
| Counting functions | |
| • Continuous counting | Yes |
| • Counter response parameterizable | Yes |
| • Hardware gate via digital input | Yes |
| • Software gate | Yes |
| Measuring functions | |
| • Dynamic measurement period adjustment | Yes |
| Measuring range | |
| — Frequency measurement, min. | 0.1 Hz |
| — Frequency measurement, max. | 25 kHz; high-speed counter mode, sinking input; 1 kHz for sourcing input, NAMUR |
| Accuracy | |
| — Frequency measurement | 100 ppm; depending on measuring interval and signal evaluation |
| Potential separation | |
| Potential separation digital inputs | |

| | |
|--|---|
| • between the channels | No |
| • between the channels and the power supply of the electronics | No |
| Potential separation digital outputs | |
| • between the channels | No |
| • between the channels and the power supply of the electronics | No |
| Isolation | |
| Isolation tested with | 1 500 V AC between PROFINET and other electronics |
| Degree and class of protection | |
| IP degree of protection | IP20 |
| Ambient conditions | |
| Ambient temperature during operation | |
| • horizontal installation, min. | -40 °C |
| • horizontal installation, max. | 70 °C; Observe derating |
| • vertical installation, min. | -40 °C |
| • vertical installation, max. | 70 °C; Observe derating |
| Ambient temperature during storage/transportation | |
| • min. | -40 °C |
| • max. | 70 °C |
| Relative humidity | |
| • Operation, max. | 95 % |
| Connection method | |
| Design of electrical connection | Connection plug |
| Dimensions | |
| Width | 329 mm |
| Height | 123 mm |
| Depth | 74 mm |
| Weights | |
| Weight, approx. | 0.7 kg |
| Classifications | |

| | Version | Classification |
|--------|---------|----------------|
| eClass | 14 | 27-24-26-90 |
| eClass | 12 | 27-24-26-90 |
| eClass | 9.1 | 27-24-26-90 |
| eClass | 9 | 27-24-26-90 |
| eClass | 8 | 27-24-92-90 |
| eClass | 7.1 | 27-24-92-90 |
| eClass | 6 | 27-24-92-90 |
| ETIM | 10 | EC002584 |
| ETIM | 9 | EC002584 |
| ETIM | 8 | EC002584 |
| ETIM | 7 | EC002584 |

Approvals / Certificates

| | | |
|--------------------------|-----|--------------------------------|
| General Product Approval | EMV | For use in hazardous locations |
|--------------------------|-----|--------------------------------|



| | |
|--------------------------------|-------------|
| For use in hazardous locations | Environment |
|--------------------------------|-------------|

[Type Examination Certificate](#)

EM



IECEX



CCC



UL



last modified:

5/16/2025 