

Eaton 183027

Catalog Number: 183027

Eaton xEffect - XNH circuit protection. NH fuse-switch 3p flange connection M8 max. 95 mm², mounting plate, light fuse monitoring, NH000 & NH00



General specifications

Product Name	Catalog Number
Eaton xEffect XNH device for mounting plate	183027
	EAN
	4015081779543
Product Length/Depth	Product Height
204 mm	84 mm
Product Width	Product Weight
106 mm	0.689 kg
Compliances	Certifications
RoHS conform	IEC/EN 60947-3

Product specifications

Type

Fuse control - light

Special features

Permanent operation (rated operating mode)

Current paths of electrolytic copper, silver-plated

With optical signalling of triggered fuse-links

Features

Halogen free

Standard sealable

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Resources

Brochures

[eaton-xeffect-xnh-fuse-switch-disconnector-brochure-br019002en-en-us.pdf](#)

Catalogs

[eaton-panel-building-accessories-catalog-ca008008en-en-us.pdf](#)

Certification reports

[eaton-xeffect-xnh-fuse-switch-disconnector-declaration-of-conformity-en-us.pdf](#)

Drawings

[eaton-circuit-breaker-xeffect-xeffect-xnh-circuit-protection-dimensions.eps](#)

eCAD model

[ETN.XNH00-FCL-A160.edz](#)

Installation instructions

[IL0131109ZU](#)

mCAD model

[eaton-XNH00-A160-drawing.dwg](#)

[eaton-XNH00-A160-3d-model.stp](#)

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Is the panel builder's responsibility.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

$U_i = 800 \text{ V AC}$

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

Fitted with:

Error protection

Frequency rating

40 Hz - 60 Hz

Pollution degree

3

Creepage resistance

CTI 600

Equipment heat dissipation, current-dependent

9 W

Rated uninterrupted current (Iu)

160 A

Total heat dissipation without fuses at Ith

9 W

Ambient operating temperature details

Ambient temperature range: -25 °C - 55 °C

Voltage rating at AC

400 V (AC-23B)

500 V (AC-22B)

690 V (AC-21B)

Voltage rating at DC

250 V DC at DC-22B

440 V DC at DC-21B

Conditioned rated short-circuit current Iq

120 kA

Number of poles

Three-pole

Rated operation power at AC-23, 400 V

0 kW

Size

NH000 / NH00 fuse

Rated impulse withstand voltage (Uimp)

8 kV

Color

Gray

Connection type

Flat connection

Degree of protection

IP2XC (contact protection, XNH installed)

IP20 (operating status, XNH installed)

IP10 (handle cover open, XNH installed)

Rated short-time withstand current (Icw)

7 kA

Direction of incoming supply

As required

Electrical connection type of main circuit

Screw connection

Activation type

Dependent manual activation

Actuator position

Front side

Actuator type

Cover grip

Voltage test

Yes, sliding inspection windows

Heat dissipation at 80% without fuses

5.8 W

Heat dissipation per pole, current-dependent

3 W

Mounting position

Vertical or horizontal

Suitable for

Ground mounting

Rated conditional short-circuit current (I_q)

120 kA

Overvoltage category

III

Suitable for fuses

NH00

Material

Polyamide

Cable entry type

Other

Frequency rating of contacts

40 Hz - 60 Hz

Mounting method

DIN rail

Mounting plate

Rated operation current (I_e)

160 A

Locking facility

Yes, optional

Flammability characteristics (UL)

Self-extinguishing (UL 94)

Degree of protection (front side)

Other

Heat deflection temperature

125 °C

Lifespan, electrical

300 operations

Lifespan, mechanical

1400 operations

Terminal capacity (copper busbar)

Bolt diameter at flange connection: M8

20 mm x 10 mm

Max. 25 mm cable lug width at flange connection

Terminal capacity (copper band)

9 mm x 0.8 mm (6x) at box terminal

Terminal capacity (stranded cable)

1.5 mm² - 50 mm² at box terminal

10 mm² - 70 mm² at clamp-type terminal

1.5 mm² - 95 mm² at box terminal

Rated operational current

160 A (AC-23B)

160 A (AC-22B)

160 A (AC-21B)

160 A

Operating altitude without derating - max

2000 mm

Permitted power loss per fuse link - max

12 W

Power rating at AC-23, 400 V

0 kW

Rated insulation voltage (Ui)

800 VAC

Rated operating voltage (Ue) at AC - max

690 V

Rated operational current for specified heat dissipation (In)

160 A

Rated conditional short-circuit rating

120 kA (500 V)

100 kA (690 V)

Terminal capacity (copper strip)

9 mm x 0.8 mm (9x) at box terminal



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia