


## M 4/6.D2.2...

## M 4/6.D2.3...


Spacing 6 mm + 0,05 (.238")



M 4/6.D2.1 equipped with 2 test sockets.

## M 4/6.D1...


Spacing 6 mm + 0,05 (.238")



M 4/6.D2.1 with vertical interconnection and partition on the lower deck.

## M 4/6.D1.1...

Spacing 6 mm + 0,05 (.238")



M 4/6.D1 with no partition on the lower deck.



Color	Type	Part numbers
Grey/Test socket DIA. 2	M 4/6.D2.2	0115 322.15
Beige V0/Test socket DIA. 2	M 4/6.D2.2.V0	0195 322.16
Grey/Test socket DIA. 3	M 4/6.D2.3	0115 269.00



Color	Type	Part numbers
Grey	M 4/6.D1	0115 166.11
Blue	M 4/6.D1.N	0125 166.13
Beige V0	M 4/6.D1.V0	0195 166.12



Color	Type	Part numbers
Grey	M 4/6.D1.1	0115 204.20
Blue	M 4/6.D1.1N	0125 204.22

## Characteristics

## Wire size

		IEC		UL	CSA
		NFC	DIN		
Compression clamp	Solid wire	0,2-4 mm <sup>2</sup>	24-10 AWG	24-10 AWG	24-10 AWG
	Stranded wire	0,22-4 mm <sup>2</sup>	24-10 AWG	24-10 AWG	24-10 AWG

## Voltage

Rated	630 V (5)	300 V	300 V
Pulse	8 kV (5)		
Pollution degree	3		

## Current

Rated	32 A	20 A	25 A
-------	------	------	------

## Wire size

Rated / Gauge	4 mm <sup>2</sup> / A4	10 AWG	10 AWG
Wire stripping length	Recomm. Screwdriver	Recomm. torque	Protection
8,5 mm	4 mm	0,5-0,8 Nm	IP20
.33"	.16"	4.4-7 lb.in	NEMA 1

Type		Part numbers
FEM6D	th. 1,0 mm	0118 499.23
FEM6D	th. 1,0 mm	0128 499.25
FEM6D V0	V0 th. 1,0 mm	0198 499.24
SCM6D	th. 1,0 mm	0113 482.05
SCM6D V0	V0 th. 1,0 mm	0193 482.06
SCF6D	th. 1,0 mm	0118 495.17
SCF6D V0	V0 th. 1,0 mm	0198 495.10
DCG	grey	0163 218.05
FC2	DIA. 2,0 mm	0007 865.26
FC4	DIA. 4,0 mm	0167 860.01

## Characteristics

## Wire size

		IEC		UL	CSA
		NFC	DIN		
Compression clamp	Solid wire	0,2-4 mm <sup>2</sup>	24-10 AWG	24-10 AWG	24-10 AWG
	Stranded wire	0,22-4 mm <sup>2</sup>	24-10 AWG	24-10 AWG	24-10 AWG

## Voltage

Rated	800 V	300 V	300 V
Pulse	8 kV		
Pollution degree	3		

## Current

Rated	32 A	20 A	25 A
-------	------	------	------

## Wire size

Rated / Gauge	4 mm <sup>2</sup> / A4	10 AWG	10 AWG
Wire stripping length	Recomm. Screwdriver	Recomm. torque	Protection
8,5 mm	4 mm	0,5-0,8 Nm	IP20
.33"	.16"	4.4-7 lb.in	NEMA 1

Type		Part numbers
FEM6D	th. 1,0 mm	0118 499.23
FEM6D	th. 1,0 mm	0128 499.25
FEM6D V0	V0 th. 1,0 mm	0198 499.24
SCM6D	th. 1,0 mm	0113 482.05
SCM6D V0	V0 th. 1,0 mm	0193 482.06
SCF6D	th. 1,0 mm	0118 495.17
SCF6D V0	V0 th. 1,0 mm	0198 495.10
AL2	(6) DIA. 2,0 mm	0163 070.00
AL3	(6) DIA. 3,0 mm	0163 261.00
DCG	grey	0163 218.05
FC2	DIA. 2,0 mm	0007 865.26

## Characteristics

## Wire size

		IEC		UL	CSA
		NFC	DIN		
Compression clamp	Solid wire	0,2-4 mm <sup>2</sup>	24-10 AWG	24-10 AWG	24-10 AWG
	Stranded wire	0,22-4 mm <sup>2</sup>	24-10 AWG	24-10 AWG	24-10 AWG

## Voltage

Rated	800 V	300 V	300 V
Pulse	8 kV		
Pollution degree	3		

## Current

Rated	32 A	20 A	25 A
-------	------	------	------

## Wire size

Rated / Gauge	4 mm <sup>2</sup> / A4	10 AWG	10 AWG
Wire stripping length	Recomm. Screwdriver	Recomm. torque	Protection
8,5 mm	4 mm	0,5-0,8 Nm	IP20
.33"	.16"	4.4-7 lb.in	NEMA 1

Type		Part numbers
FEM6D	th. 1,0 mm	0118 499.23
FEM6D	th. 1,0 mm	0128 499.25
FEM6D V0	V0 th. 1,0 mm	0198 499.24
SCM6D	th. 1,0 mm	0113 482.05
SCM6D V0	V0 th. 1,0 mm	0193 482.06
SCF6D	th. 1,0 mm	0118 495.17
SCF6D V0	V0 th. 1,0 mm	0198 495.10
AL2	(1) (6) DIA. 2,0 mm	0163 070.00
AL3	(1) (6) DIA. 3,0 mm	0163 261.00
DCG	grey	0163 218.05
FC2	DIA. 2,0 mm	0007 865.26

BJM6D	(2) (6)	2 poles	0173 515.11
BJM6D	(2) (6)	3 poles	0173 516.12
BJM6D	(2) (6)	4 poles	0173 517.13
BJM6D	(2) (6)	5 poles	0173 519.25
BJM6D	(2) (6)	10 poles	0173 520.22
BJMI6D	(2) (6)	2 poles	0179 668.20
BJMI6D	(2) (6)	3 poles	0179 669.21
BJMI6D	(2) (6)	4 poles	0179 670.26
BJMI6D	(2) (6)	5 poles	0179 671.13
BJMI6D	(2) (6)	10 poles	0179 672.14
EL6			0173 627.21
BJS61	(2) (4) (6)	10 poles	0168 485.27
EV6D			0168 400.16
BJP61	(6)		0167 225.20
PC61		10 poles	0163 311.22
AD2,5			0114 205.20

BJM6D	(1) (6)	2 poles	0173 515.11
BJM6D	(1) (6)	3 poles	0173 516.12
BJM6D	(1) (6)	4 poles	0173 517.13
BJM6D	(1) (6)	5 poles	0173 519.25
BJM6D	(1) (6)	10 poles	0173 520.22
BJMI6D	(1) (6)	2 poles	0179 668.20
BJMI6D	(1) (6)	3 poles	0179 669.21
BJMI6D	(1) (6)	4 poles	0179 670.26
BJMI6D	(1) (6)	5 poles	0179 671.13
BJMI6D	(1) (6)	10 poles	0179 672.14
EL6			0173 627.21
BJS61	(1) (4) (6)	10 poles	0168 485.27
EV6D			0168 400.16
BJP61	(6)		0167 225.20
PC61		10 poles	0163 311.22
AD2,5			0114 205.20

PC61		10 poles	0163 311.22
AD2,5			0114 205.20
CBM5D	th. 0,5 mm		0173 530.24

(1) Sides of block

(1) Sides of block (2) Top of block

(1) Sides of block (2) Top of block

Note : (1) A circuit separator SC may be required with the use of these accessories. (2) Use of these accessories requires the user to cut out the partition. (4) See section Accessories for other configuration of poles. (5) Only for block M 4/6.D2.2. 200V/2,5 kV for blocks M 4/6.D2.3 and M 4/6.D2.4. (6) These accessories can be used on the lower deck only.