AUTOMOTIVE GRADE

COMPLIANT

HALOGEN FREE




Vishay General Semiconductor

Ultrafast Avalanche Surface Mount Rectifiers



TO-277A (SMPC)



PRIMARY CHARACTERISTICS					
I _{F(AV)}	2.0 A				
V_{RRM}	800 V, 1000 V				
I _{FSM}	30 A				
t _{rr}	75 ns				
E _{AS}	20 mJ				
V _F at I _F = 2.0 A	1.42 V				
T _J max.	175 °C				
Package	TO-277A (SMPC)				
Diode variations	Single die				

TYPICAL APPLICATIONS

For use in lighting, fast switching rectification of power supplies, inverters, converters, and freewheeling diodes for consumer, automotive, and telecommunication.

FEATURES

- Very low profile typical height of 1.1 mm
- · Ideal for automated placement
- · Glass passivated chip junction
- Fast reverse recovery time
- Controlled avalanche characteristics
- · Low leakage current
- High forward surge capability
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- AEC-Q101 qualified
- Material categorization: For definitions of compliance please see www.vishay.com/doc?99912

MECHANICAL DATA

Case: TO-277A (SMPC)

Molding compound meets UL 94 V-0 flammability rating Base P/N-M3 - halogen-free, RoHS-compliant, and

commercial grade

Base P/NHM3 - halogen-free, RoHS-compliant, and automotive grade

actornotivo grado

Terminals: Matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

M3 suffix meets JESD 201 class 2 whisker test, HM3 suffix meets JESD 201 class 2 whisker test

MAXIMUM RATINGS (T _A = 25 °C unless otherwise noted)					
PARAMETER		SYMBOL	AU2PK	AU2PM	UNIT
Device marking code			AU2K	AU2M	
Maximum repetitive peak reverse voltage		V _{RRM}	800	1000	V
Maximum DC forward current (fig. 1)		I _F ⁽¹⁾	2.0		A
		I _F ⁽²⁾	1.3		
Peak forward surge current 10 ms single half sine-wave superimposed on rated load		I _{FSM}	30		А
Non-repetitive avalanche energy at T _J = 25 °C	$I_{AS} = 2.5 A \text{ max}.$	E _{AS}	20		— mJ
	$I_{AS} = 1.0 A \text{ typ.}$	LAS	30		
Operating junction and storage temperature range		T _J , T _{STG}	- 55 to + 175		°C

Notes

- (1) Mounted on 10 mm x 10 mm pad areas, 1 oz. FR4 PCB
- (2) Free air, mounted on recommended pad area



Vishay General Semiconductor

ELECTRICAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)						
PARAMETER	TEST CONDITIONS		SYMBOL	TYP.	MAX.	UNIT
Instantaneous forward voltage	I _F = 2.0 A	T _A = 25 °C	V _F ⁽¹⁾	2.1	2.5	V
		T _A = 125 °C		1.42	2.0	
Reverse current	Rated V _R	T _A = 25 °C	I _R ⁽²⁾	0.27	10	μА
		T _A = 125 °C		62	500	
Maximum reverse recovery time	$I_F = 0.5 \text{ A}, I_R = 1.0 \text{ A},$ $I_{rr} = 0.25 \text{ A}$		t _{rr}	50	75	ns
Typical junction capacitance per diode	Rated V _R = 4.0 V, 1 MHz		CJ	29	-	pF

Notes

 $^{(1)}$ Pulse test: 300 μs pulse width, 1 % duty cycle

(2) Pulse test: Pulse width ≤ 40 ms

THERMAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)					
PARAMETER	SYMBOL	AU2PK AU2PM		UNIT	
Typical thermal resistance	R _{0JA} (1)	85		°C/W	
	R _{0JM} (2)	5			

Notes

 $^{(1)}\,$ Free air, mounted on recommended PCB 1 oz. pad are; thermal resistance $R_{\theta JA}$ - junction to ambient

 $^{(2)}$ Units mounted on PCB with 10 mm x 10 mm copper pad areas; $R_{\theta JM}$ - junction to mount

ORDERING INFORMATION (Example)						
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE		
AU2PM-M3/86A	0.10	86A	1500	7" diameter plastic tape and reel		
AU2PM-M3/87A	0.10	87A	6500	13" diameter plastic tape and reel		
AU2PMHM3/86A (1)	0.10	86A	1500	7" diameter plastic tape and reel		
AU2PMHM3/86A (1)	0.10	87A	6500	13" diameter plastic tape and reel		

Note

(1) AEC-Q101 qualified

Vishay General Semiconductor

RATINGS AND CHARACTERISTICS CURVES

(T_A = 25 °C unless otherwise noted)




Fig. 1 - Maximum Forward Current Derating Curve




Fig. 2 - Average Power Loss Characteristics




Fig. 3 - Typical Instantaneous Forward Characteristics




Fig. 4 - Typical Reverse Leakage Characteristics




Fig. 5 - Typical Junction Capacitance





Fig. 6 - Typical Transient Thermal Impedance



Vishay General Semiconductor

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)





Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.

Revision: 02-Oct-12 Document Number: 91000