

# UC-WMCO 1,6 (12X3) GN - Conductor marker



0827515

<https://www.phoenixcontact.com/gb/products/0827515>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Conductor marker, Sheet, green, unlabeled, can be labeled with: BLUEMARK E.CARD, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, cable diameter range: 1.3 ... 1.6 mm, mounting type: slide-on, Number of individual labels: 40, text field height: 3 mm, text field width: 12 mm

## Your advantages

- The markers, which are supplied in uniform sheets, can be printed onto quickly and easily using the BLUEMARK printing systems
- The UC-WMCO ... UniCard labeling range includes thread-on markers for the subsequent labeling of conductors by simply sliding them on using the UC-WMCO ... TOOL
- The format automatically ensures printing with a high degree of positioning accuracy
- Secure tight fit even in the event of vibrations
- Large-surface labeling option in a space-saving design
- The sheets provide space for including function texts
- Marking service: Phoenix Contact can custom-mark all UniCard markers according to your specifications

## Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 0827515             |
| Packing unit                         | 10 pc               |
| Minimum order quantity               | 10 pc               |
| Sales key                            | BG2217              |
| Product key                          | BG2217              |
| Catalog page                         | Page 206 (C-3-2017) |
| GTIN                                 | 4046356439923       |
| Weight per piece (including packing) | 8.2 g               |
| Weight per piece (excluding packing) | 7.2 g               |
| Customs tariff number                | 39269097            |
| Country of origin                    | PL                  |

# UC-WMCO 1,6 (12X3) GN - Conductor marker



0827515

<https://www.phoenixcontact.com/gb/products/0827515>

## Technical data

### Product properties

|              |                   |
|--------------|-------------------|
| Product type | Conductor marking |
| Type         | Card form         |

### Marking

|                                     |                   |
|-------------------------------------|-------------------|
| Number of individual labels         | 40                |
| Number of individual labels per row | 10                |
| Identification technology           | UV LED technology |

### Dimensions

|        |        |
|--------|--------|
| Width  | 12 mm  |
| Height | 3.2 mm |
| Depth  | 3.3 mm |

### External dimensions

|                  |                   |
|------------------|-------------------|
| Outside diameter | 1.3 mm ... 1.6 mm |
|------------------|-------------------|

### Text field

|                   |       |
|-------------------|-------|
| Text field width  | 12 mm |
| Text field height | 3 mm  |

### Material specifications

|                                                                         |                                |
|-------------------------------------------------------------------------|--------------------------------|
| RoHS compliant                                                          | yes                            |
| Color                                                                   | green (RAL 6021)               |
| Material                                                                | PA                             |
| Flammability rating according to UL 94                                  | V2                             |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 120 °C                         |
| Fire protection for rail vehicles (DIN EN 45545-2) R22                  | HL 1 - HL 2                    |
| Fire protection for rail vehicles (DIN EN 45545-2) R23                  | HL 1 - HL 2                    |
| Fire protection for rail vehicles (DIN EN 45545-2) R24                  | HL 1 - HL 2                    |
| Components                                                              | free from silicone and halogen |

### Cable/line

|                         |                   |
|-------------------------|-------------------|
| External cable diameter | 1.3 mm ... 1.6 mm |
|-------------------------|-------------------|

### Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

### UV resistance

|               |                                |
|---------------|--------------------------------|
| Specification | ISO 4892-2:2013-03 (following) |
| Result        | Test passed                    |

# UC-WMCO 1,6 (12X3) GN - Conductor marker



0827515

<https://www.phoenixcontact.com/gb/products/0827515>

|               |      |
|---------------|------|
| Test duration | 96 h |
|---------------|------|

## Wipe resistance of inscriptions

|                                                 |                                                                                       |
|-------------------------------------------------|---------------------------------------------------------------------------------------|
| Specification                                   | DIN EN 61010-1 (VDE 0411-1):2011-07<br>DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropyl<br>[CAS No. 67-63-0]                  | Test passed                                                                           |
| n-Hexane<br>[CAS No. 110-54-3]                  | Test passed                                                                           |
| Water + Petroleum ether<br>[CAS No. 64742-82-1] | Test passed                                                                           |

## Testing in a condensation changing climate in the presence of sulfur dioxide

|               |                   |
|---------------|-------------------|
| Specification | DIN 50018:2013-05 |
| Result        | Test passed       |
| Climate level | AHT 1.0 S         |
| Cycles        | 2                 |

## Salt spray test

|               |                           |
|---------------|---------------------------|
| Specification | DIN EN 60068-2-11:2000-02 |
| Result        | Test passed               |

## Ambient conditions

|                                                     |                                                                                                         |
|-----------------------------------------------------|---------------------------------------------------------------------------------------------------------|
| Ambient temperature (operation)                     | -40 °C ... 120 °C                                                                                       |
| Recommended storage conditions                      | 23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended. |
| Recommended ambient temperature (storage/transport) | 23 °C                                                                                                   |
| Recommended humidity (storage/transport)            | 50 %                                                                                                    |

## Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

## Standards

|                       |            |
|-----------------------|------------|
| Standards/regulations | EN 45545-2 |
|-----------------------|------------|

## Mounting

|               |          |
|---------------|----------|
| Mounting type | slide-on |
|---------------|----------|

# UC-WMCO 1,6 (12X3) GN - Conductor marker



0827515

<https://www.phoenixcontact.com/gb/products/0827515>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281102 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001530 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

# UC-WMCO 1,6 (12X3) GN - Conductor marker



0827515

<https://www.phoenixcontact.com/gb/products/0827515>

## Environmental product compliance

|                                         |                            |
|-----------------------------------------|----------------------------|
| EU RoHS                                 |                            |
| Fulfills EU RoHS substance requirements | Yes, No exemptions         |
| EU REACH SVHC                           |                            |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt% |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)