



**VECTOR**

Custom Laser Solutions

Featuring the  
NEW


# Variable Line Length Laser

a revelation in  
control, convenience  
and customer  
confidence.

FOCUS CONTROL



LINE LENGTH  
CONTROL



# VECTORLYTE ALIGNMENT SYSTEM COMPONENTS



**MOUNTING KIT- MK1** This mount holds the laser module in a clamp which rotates on a ball headed rod of 2.3/8ins.(60mm) length. A second clamp allows the rod to slide to different positions and to be fixed to any surface using the screws provided.



## BRACKETS

Brackets are available with holes at regular intervals.


- B12** - 30cm/12"
- B6** - 15cm/6"
- B4** - 10cm/4"
- B2** - right angled 10cm/4"
- BS** - one of each



## POWER SUPPLIES

**PS-1** for 1 laser and  
**PS-4** for up to 4 lasers.

Two power supplies are available; both comply with the legal requirements of LED on/off indicator. Both are fully Radio and High Frequency protected as is the rest of the system.



## LASER MODULE

Please see the table below for details of the laser powers and projections. The laser modules have a plug on the back of the module. A cable of 1.5m/6ft is supplied with each module. Extension leads are also available. Each module has focus and line length adjustment features. The modules are Radio and High Frequency protected.

## EXTENSION LEADS

### EXT3

3m/10ft extension leads are available as standard. Any length can be ordered.

**Control, Convenience and Confidence...** Now it's easy to choose the best laser for your needs. Remember, there is no need to compromise between the length of the laser line you require, and the most convenient mounting position. Mount the laser and then adjust the power and length of line to suit you. For full instructions on the choice and use of the LaserLyte system please see our web site.

## TABLE OF AVAILABLE PROJECTIONS

PART NOS*	POWERS	PROJECTIONS	RANGE OF VISIBILITY IN YARDS OR METRES			
			30 Min. Fan Angle		80 Max. Fan Angle	
			Distance from surface	Line Length	Distance from surface	Line Length
Includes MK1						
<b>V5 D</b>	<b>Standard Power</b> 650nm-1-5mW	Dot				
<b>V5 Dvi</b>		Dot with Variable Intensity				
<b>V5 VLL</b>		Variable Length Line	2	1	1	2
<b>V5 LL+D</b>		Long Line with Centre Dot			1	2
<b>V5 RXL</b>		Crossed Lines with Rotating Axis				
<b>V5 Xvi</b>		Small Cross with Variable Intensity				
<b>V3 LL</b>	<b>Bright Power</b> 635nm-5mW	Variable Length Line	4	2	2.5	4
<b>V3 LL+D</b>		Long Line with Centre Dot			2.5	4
<b>V3 RXL</b>		Crossed Lines with Rotating Axis				
<b>V3 Xvi</b>		Small Cross with Variable Intensity				
<b>V2 VLL</b>	<b>Super Bright</b> 635nm-10mW	Variable Length Line (other projections available to order)	5	2.5	3.5	6
<b>V1 VLL</b>		<b>Ultra Bright</b> 635nm-15mW	Variable Length Line (other projections available to order)	6	3	4

\*These parts numbers include a laser module, 1.5m/6ft cable, MK1 Mounting Kit + Focusing Key

## KEY TO PROJECTIONS

- D** = Dot; which you can now focus to a precise spot at any distance
- Dvi** = Dot; which you can both focus to a precise spot at any distance, and vary the intensity
- VLL** = Variable Length Line; you can double the length of the line by adjusting the fan angle to spread light from 30 to 80
- LL+D** = Long 80 line with a central dot enabling both vertical and horizontal alignment
- RXL** = Rotating Lines which can be adjusted to intersect at any angle, from any angle of mounting



A GLOBAL LASER TECHNOLOGY GROUP COMPANY

Technology Centre. Medialion House, Cwmtillery, Gwent  
South Wales NP13 1LZ UK  
**Tel:** 44 (0) 1495 212213 **Fax:** 44 (0) 1495 214004  
**e:mail:** info@globalasertech.com

## OUR SERVICE TO YOU

- Website:** www.globalasertech.com
- Warranty** for a full year
- Shipping** and customs clearance by UPS
- Delivery** 48 hours worldwide, from stock

