

WIRE MANAGEMENT PRODUCTS

QQ-W-343E
QQ-B-575B

TINNED COPPER BRAID FLAT, OVAL

CHOOSE TINNED COPPER BRAID FOR:

- Ground/Shielding Terminations



TINNED COPPER BRAID APPLICATIONS:

- Point-to-Point Ground Path
- Wire/Cable Shielding

CHARACTERISTICS

PRODUCT DESCRIPTION:

- Flat or Oval Shaped Tinned Copper Braid



SHIELDING, GROUND STRAP:

A tight weave of multi-strand, soft drawn tinned copper wire; tinned copper braid is an ideal shielding material for short-run cables providing easy radial termination. In retrofit applications, provides additional shielding efficiency. Tinned copper flat braid, used as a ground strap, provides an excellent, low-resistance ground path.

159

TINNED COPPER FLAT BRAID

Alpha Part No.	Nom. Flat Width		Nom. Thickness		Braid Construction		Approx. AWG Equiv.	Nom. Circular Mil Area, CM	Approx. Current Carrying Cap. (Amps)†	Standard Package Spools Ft.
	Inches	mm	Inches	mm	AWG of Indiv. Ends	Total No. of Indiv. Carriers				
1221	0.025	0,63	0.015	0,38	36	8	27	200	4	100, 500, 1000
1222	1/32	0,79	0.020	0,50	36	16	24	400	6	100, 500, 1000
1223†	3/64	1,19	0.020	0,50	36	24	22	600	7	100, 500, 1000
1224	3/32	2,38	0.020	0,50	36	16	19	1200	11	100, 500, 1000
1229†	1/8	3,18	0.020	0,50	36	24	18	1800	16	100, 500, 1000
1230†	3/16	4,76	0.020	0,50	36	24	15	3000	25	100, 500, 1000
1231†	1/4	6,35	0.030	0,76	36	24	14	4200	32	100, 500, 1000
1232	3/8	9,53	0.030	0,76	36	48	12	7200	46	100, 500, 1000
1233/2	1/2	12,70	0.030	0,76	36	48	10	9600	53	100, 500, 1000
1233†	5/8	15,90	0.030	0,76	36	48	10	9600	53	100, 500, 1000
1234	3/4	19,10	0.040	1,02	36	48	7	20800	85	100, 500, 1000
1235	1	25,40	0.045	1,14	36	48	7	20800	85	100, 500, 1000
1239†	1-3/8	34,90	0.050	1,27	30	48	5	33700	100	100, 500, 1000
1240†	1-1/2	38,10	0.060	1,52	30	48	3	53064	150	100
1241	1-3/4	44,50	0.080	2,03	30	48	2/0	125424	280	100
1242	2	50,80	0.120	3,05	30	48	3/0	154368	310	100
1242/4	3	76,20	0.200	5,08	30	48	4/0	225000	390	100

SPECIFICATIONS

- QQ-W-343E
- ASTM-B-33
- † Meets QQ-B-575B

TINNED COPPER OVAL BRAID

Alpha Part No.	Nom. I.D. When Rounded		Braid Construction		Approx. AWG Equiv.	Nom. Circular Mil Area, CM	Approx. Current Carrying Cap. (Amps)†	Standard Package Spools Ft.
	Inches	mm	AWG of Indiv. Ends	Total No. of Indiv. Carriers				
2132	1/16	1,59	34	16	32	19	1192	11
2138	11/64	4,37	34	24	120	14	4770	32
2140	3/16	4,76	34	24	144	13	5724	38
2142	1/4	6,35	34	24	168	12	6678	41
2144	3/8	9,53	34	24	192	11	7632	46
2146	1/2	12,70	34	48	336	9	13356	62
2148	5/8	15,88	34	48	384	8	14264	64
2150	11/16	17,46	34	48	480	7	19080	81
2152	25/32	19,84	34	48	528	7	20988	85

†Values shown are for bare cable in free air at 30°C (86°F) and intended as a reference guide only. Actual values will depend on permissible temperature rise, permissible voltage drop and other conditions of service.