

FEATURES

- **Polytetrafluoroethylene material:** Provides excellent chemical resistance and durability
- **Maximum operating pressure of 3000 kPa:** Suitable for high-pressure applications
- **Maximum operating temperature of 280 °C:** Ensures performance in high-temperature environments
- **Rotary speed of 18 m/s:** Supports high-speed operations
- **20 mm section:** Offers robust sealing capability
- **8 m length:** Provides ample material for various applications

RS PRO 8m Polytetrafluoroethylene Gland Packing, 20mm Section

RS Stock No: 606-550



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO gland packing is designed for sealing applications in industrial environments. Made from high-quality polytetrafluoroethylene, it offers exceptional chemical resistance and durability. Ideal for use in high-pressure and high-temperature settings, this gland packing ensures reliable performance and longevity.

General Specifications

Maximum Operating Pressure	3000 kPa
Product Type	Gland & Valve Packing
Rotary Speed	18 m/s
Section	20 mm
Sub Type	Gland Packing

Mechanical Specifications

Length	8 m
Material	Polytetrafluoroethylene

Operation Environment Specifications

Maximum Operating Temperature	280 °C
-------------------------------	--------

Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, BAM, FDA, RoHS
---------------------	--------------------------------------