



Monitoring relay - motor temperature monitoring

Status: **Available** Data sheet created: **01.07.2025**

Item Number: 2390102 - Serie: Gamma - EAN: 9008662002388



- ✓ Monitoring relays GAMMA series
- ✓ Motor temperature monitoring (PTC)
- ✓ Galvanic isolation to the sensor circuit
- ✓ Fault memory
- ✓ Test and reset button
- ✓ External reset button connectable
- ✓ Supply voltage 230V AC
- ✓ 1 changeover contact
- ✓ width 22,5mm
- ✓ Industrial design

Description

Temperature monitoring of the motor winding (max. 6 PTC) with fault latch, for temperature probes in accordance with DIN 44081 Test function with integrated test/reset key.

General information


Short description	Motor temperature monitoring, 1 changeover contact, 230V AC
Item Number	2390102
EAN	9008662002388
Main category	Monitoring Relays
Series	Gamma
Type	G2TF01 230VAC
Design	Industrial design
Supply	230V AC
Dimensions	22.5 x 18 x 90 mm



Functions and measurands

Amount of functions

1



Temperature monitoring of the motor winding with fault latch (TEMP)

If the PTC sum resistance is less than 3.6 k Ω (normal temperature of the motor) when the supply voltage U is applied (green LED illuminated), the output relay switches into on-position. can be tested in the event of a fault. With an external reset button, the test function is not effective. If the total resistance rises above 3.6 k Ω (at least one of the PTCs has reached the nominal switch-off temperature), the output relay drops out (red LED lights up). The output relay R switches back on or the error is cleared (red LED not illuminated) when, after the PTCs have cooled down, the total resistance has fallen below 1.8 k Ω again and either a reset button (internal or external) is pressed or the voltage supply is switched off and applied again.

Indicators

Supply/time lapse 1	Green LED U ON: Supply voltage applied
Error / monitoring function	Red LED ON/OFF: Display error for corresponding threshold

Mechanical design

Housing material	made of self-extinguishing plastic
Housing - protection degree	IP40
Mounting	top hat rail TH 35 7,5-15 according to IEC 60715:2017 / EN 60715:2017
Terminals/connections	Touch-proof clamping yoke terminals according to DGUV 3 (Screwdriver PZ1 required)
Terminals - protection degree	IP20
Mounting position	any
Stripping length	7 mm
Max. Tightening Torque	1 Nm
Terminal capacity	<ul style="list-style-type: none"> • 1 x 0.5 to 2.5mm² with/without ferrule • 1 x 4mm² without ferrule • 2 x 0.5 to 1.5mm² with/without ferrules • 2 x 2.5mm² flexible without ferrules

Supply circuit

Terminals/connections	A1-A2 (galvanically separated)
Supply voltage a.c.	selectable via power supply
Supply voltage tolerance a.c.	According to power supply unit specification
Rated consumption a.c.	1,5 W / 2 VA
Rated frequency power module	According to power supply unit specification
Duty cycle	100%
Recovery time	500 ms
Drop-out voltage	>30% the supply voltage
Overvoltage category	III (IEC 60664-1)
Rated surge voltage	4 kV
Rated impulse withstand voltage	400 V a.c.



Output circuit

Type	Relay
Contact 1	1 change over contact
Terminals 1	11-12-14
Rated voltage	250 V a.c.
conditional short-circuit current	1 kA
Mechanical life	15 x 10 ⁶ Switching cycles
Electrical life	100 x 10 ³ Switching cycles (1000 VA)
Utilization categorie	AC 15
Switching frequency	max. 60/min at 100 VA resistive load
Switching frequency 2	max. 6/min at 1000 VA resistive load (IEC 60947-5-1)
Rated surge voltage	4 kV
Overvoltage category	III (IEC 60664-1)

Control input

Function	external reset key
Loadable	no
Maximum line length	R-T2: max. 10m (twisted pair)
Reset	potential free normally open contact, terminals R-T2

Measuring circuit

Measurand	Temperature
-----------	-------------

Accuracy

Base accuracy	±10 % (from full scale)
Repetition accuracy	≤1 %
Voltage influence	≤2.2 % / V
Temperature influence	≤0.1 % / °C

Measuring circuit - temperature

Measuring input	Terminals T1-T2
Initial resistance	<1.5 kΩ
Response value (relay in off-position)	≥3.6 kΩ
Release value (relay in on-position)	≤1.8 kΩ
Disconnection (short circuit thermistor)	no
Measuring voltage T1-T2	≤2.5 V d.c. at R ≤4.0 kΩ (according to DIN VDE 0660 part 302)
Overvoltage category	III (according to IEC 60664-1)
Rated surge voltage	4 kV



Ambient conditions and general specifications

Ambient temperature IEC	-25 ... +55°C (IEC 60068-1)
Ambient temperature UL	-25 ... +40°C (UL 508)
Storage temperature	-25 ... +70 °C
Transport temperature	-25 ... +70 °C
Relative humidity	15% ... 85% (IEC 60721-3-3 class 3K3)
Vibration resistance	10 ... 55 Hz 0.35 mm (IEC 60068-2-6)
Shock resistance	15 g 11 ms (IEC 60068-2-27)
Pollution degree	3 (IEC 60664-1)
Installation altitude	Up to 2000 m above sea level

Logistics

Minimum Quantity	1
Tariff Number	85364900
EAN	9008662002388
Country of Origin	AT
Product Weight (g)	179

Available declarations / conformities


EAC	✓
CE	✓
UL	Open document
c(UL)	Open document
REACH	Open document
WEEE	Open document
TSCA	Open document
RoHs	Open document
CMRT	Open document



CAD Files

STEP_G2_en.STEP	Download file
-----------------	-------------------------------



Media & drawings





Tele Haase Steuergeräte Ges.m.b.H
Vorarlberger Allee 38
1230 Vienna
Austria

CALL US



+43 / 1 / 614 74 - 0

ONLINE SUPPORT



support@tele-haase.at

Changes and errors excepted