



**Part Number :** [2032631334](#)  
**Product Description :** Sentrality 3.40mm Surface Mount Pin, 14.00mm Engagement Length, Bag  
**Series Number :** 203263  
**Status :** Active  
**Product Category :** PCB Headers and Receptacles



## Documents & Resources

### Drawings

[2032631334\\_sd.pdf](#)  
[2032630006-PK-000.pdf](#)

### 3D Models and Design Files


[STEP AP242](#)  
[SOLIDWORKS](#)  
[Creo](#)  
[Symbol and Footprint \(Multi-Format\)](#)

### Specifications

[2043130018-AS-000.pdf](#)  
[2043130018-PS-000.pdf](#)  
[2043131234-TS-000.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not saleable
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	PCB Headers and Receptacles
Series	203263
Description	Sentrality 3.40mm Surface Mount Pin, 14.00mm Engagement Length, Bag
Application	Board-to-Board, Busbar-to-Board, Busbar-to-Busbar, Power
Component Type	PCB Header
Product Name	Sentrality
UPC	193264058136

### Electrical

Current - Maximum per Contact	75.0A
Voltage - Maximum	600V

### Physical

Breakaway	No
Circuits (Loaded)	1
Circuits (maximum)	1
Diameter	3.40mm

Durability (mating cycles max)	200
Glow-Wire Capable	No
Guide to Mating Part	No
Height Above Board	14.00mm
Material - Metal	Copper Alloy
Material - Plating Mating	Silver
Material - Plating Termination	Silver
Net Weight	1.522/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Bag
PCB Retention	None
Pitch - Mating Interface	N/A
Polarized to Mating Part	No
Polarized to PCB	No
Temperature Range - Operating	-40° to +125°C
Termination Interface Style	Surface Mount

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
Sentrality Top-entry Surface Mount Socket Assemblies	<a href="#"><u>204318</u></a>
Sentrality Top-entry Surface Mount Socket Assemblies with Self-alignment Capability	<a href="#"><u>204365</u></a>
Sentrality Top-entry Knurled Press-Fit Socket Assemblies with Self-alignment Capability	<a href="#"><u>204313</u></a>
Sentrality Top-entry Knurled Press-Fit Socket Assemblies	<a href="#"><u>204316</u></a>
Sentrality 3.40mm Right-Angle Socket Assemblies	<a href="#"><u>205000</u></a>