



Pushing Performance
Since 1945

AIDA H-distributor



Image is for illustration purposes only. Please refer to product description.

Part number	61 12 204 0001 02
Specification	AIDA H-distributor
HARTING eCatalogue	https://harting.com/6112204000102

Identification

Category	Energy distributors
Series	Han® PushPull (V14)
Identification	AIDA H-distributor
Element	Energy distributor
Specification	Distributor
	With 4x PushPull interface
	AIDA compliant
Features	Intuitive locking mechanism

Version

Termination method	Han® PushPull (V14)
Number of contacts	5
Locking type	PushPull
Pack contents	Distributor
	2 fixing screws
	4 Transport protection covers
	2 distance sleeves

Technical characteristics

Rated current	15 A
Rated voltage	24 V
Rated impulse voltage	4 kV
Pollution degree	3
Limiting temperature	0 ... +55 °C



Pushing Performance
Since 1945

Technical characteristics

Storage temperature	-40 ... +70 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (insert)	Polyamide (PA)
Material (contacts)	Copper alloy
Material (hood/housing)	Zinc die-cast
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Commercial data

Packaging size	1
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140223899
eCl@ss	27440190 Industry connector (unspecified)
ETIM	EC001264
UNSPSC 24.0	39121409