

GPEG SO - Engraving material



0811794

<https://www.phoenixcontact.com/gb/products/0811794>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Engraving material, Sheet, according to customer requirement, labeled according to customer specifications, mounting type: adhesive, text field height: 277 mm, text field width: 293 mm



Commercial data

Item number	0811794
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BG2415
Product key	BG2415
GTIN	4017918929688
Weight per piece (including packing)	152.44 g
Weight per piece (excluding packing)	152.44 g
Customs tariff number	39203000
Country of origin	PL

Technical data

Product properties

Product type	Labeled device marker
--------------	-----------------------

Environmental and real-life conditions

UV resistance

Specification	ISO 4892-2:2013-03 (following)
---------------	--------------------------------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
---------------	-------------------------------------

Ambient conditions

Ambient temperature (operation)	-20 °C ... 85 °C
Recommended storage conditions	20°C/50% relative humidity. Storage in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	20 °C
Recommended humidity (storage/transport)	50 %
Shelf life	12 months

Mounting

Mounting type	adhesive
---------------	----------

Material specifications

Adhesive strength	50 µm
Adhesive	Acrylic
Color	according to customer requirement
Material	ABS
Components	Silicone-free

Environmental and real-life conditions

UV resistance

Specification	ISO 4892-2:2013-03 (following)
---------------	--------------------------------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
---------------	-------------------------------------

Ambient conditions

Ambient temperature (operation)	-20 °C ... 85 °C
Recommended storage conditions	20°C/50% relative humidity. Storage in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	20 °C
Recommended humidity (storage/transport)	50 %
Shelf life	12 months

GPEG SO - Engraving material



0811794

<https://www.phoenixcontact.com/gb/products/0811794>

Dimensions

Width	300 mm
Length	280 mm
Material strength	0.80 mm

Text field

Text field width	293 mm
Text field height	277 mm

GPEG SO - Engraving material



0811794

<https://www.phoenixcontact.com/gb/products/0811794>

Classifications

ECLASS

ECLASS-13.0	27281103
-------------	----------

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

GPEG SO - Engraving material



0811794

<https://www.phoenixcontact.com/gb/products/0811794>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd

Halesfield 13, Telford

Shropshire, TF7 4PG

01952 681700

info@phoenixcontact.co.uk