

Floor standing polyester enclosure, PanelSeT PLA, open bottom, ventilated canopy, 500x750x420mm, IP44, IK10

NSYPLAZT574G

Main

Range	PanelSeT	
product name	PanelSeT PLA	
Enclosure type	Multi-purpose	
Product or component type	Suitable enclosure	
Version	PLAZT	
Nominal height	500 mm	
Nominal width	750 mm	
Nominal depth	420 mm	
Enclosure mounting	Floor-standing	
Device composition	1 top part 1 bottom part 2 side part 1 rear panel 1 door 1 canopy 1 plinth	

Complementary

Body type	Open top and bottom part assembled with side parts	
Door type	Plain front	
Number of doors	1 door(s)	
Door opening side	Reversible (180 °)	
Lock type	2 points handle lock, 5 mm double-bar	
Accessibility for operation	Rear	
	Front	
	Тор	
	Bottom	
Removable parts	Door by hinges	
	Rear panel by fixing element	
	Canopy by fixing element	
Material	Polyester reinforced with fibreglass	
Colour	Grey (RAL 7035)	
Standards	IEC 62208	
Product certifications	Veritas	
Electrical insulation class	Class II	

Environment

IP degree of protection	IP44 conforming to IEC 60529 (with plinth type open bottom part and ventilated canopy)	
IK degree of protection	IK10 conforming to IEC 62262 (plain door)	
Fire resistance	960 °C conforming to IEC 62208	
Ambient air temperature for storage	-3590 °C	
Packing Units		
Unit Type of Package 1	PCE	
Number of Units in Package 1	1	
Package 1 Height	46.000 cm	
Package 1 Width	60.000 cm	
Package 1 Length	79.000 cm	
Package 1 Weight	24.200 kg	
Unit Type of Package 2	PAM	
Number of Units in Package 2	4	

135.000 cm

100.000 cm

120.000 cm

112.000 kg

Package 2 Height

Package 2 Width

Package 2 Length

Package 2 Weight



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∅ Environmental footprint		
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	188	
Environmental Disclosure	Product Environmental Profile	

Use Better

Materials and Packaging	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	1341ad4e-77b9-40e3-bab0-32043fbc5959
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

Technical Illustration

Dimensions

