



Main

Range of product	OsiSense XG
Accessory / separate part category	Connection accessories
Accessory / separate part type	Connecting cable
Accessory / separate part designation	Pre-wired M12 female connector
Accessory / separate part destination	For 24 V DC supply of connection box
Cable length	10 m

Complementary

Product compatibility	XGSZ33ETH TCSAMT31FP
Electrical connection	1 female connector M12 4 pins A coding
Colour	Black
Net weight	0.52 kg

Environment

IP degree of protection	IP67
-------------------------	------

Packing Units

Package 1 Weight	343 g
Package 2 Weight	3.896 kg

Offer Sustainability


REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Wiring Diagram

Modbus Connections



Pin no.		Signal
1	Red	+ 24 VDC
2	NC	-
3	Black	0 VDC
4	NC	-