


Special

*Image for illustrative purpose only*

Summary

[Request a quote](#)[00and01Coaxial en](#)[Customer Drawing](#)

Nb of contacts Coax	1
Socket / Receptacle	Socket / Receptacle - Elbow
Locking system	Push-pull
Panel Drill Hole	M7
Size	00
Suggested matching part	FVS.00.250.NTA
Series	00 - NIM-CAMAC

https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/eps-00-250-ntn.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Nb of contacts Coax	1
R (max)	6.1 mOhm
Insert configuration value	00.25 - 1 Coax (50 Ohm)
Footprint IPC Class3 compatibility	Yes
Class3 Productibility Level Compatibility	A (General Design Producibility - Preferred)
Insulator	T: PTFE
Rated current	4 A
Impedance	50 Ohms
VSWR	$1.09 + 0.11 * f/\text{GHz}$
Vtest	2100 V (AC), 3000 V (DC)
Test voltage	2.1 kV (rms)
Contact Dia.	0.7 mm (0.028in)

Form & Material

Shell style / Model id	EPS - Elbow receptacle with two nuts, for printed circuit
Socket / Receptacle	Elbow
Housing material	Brass (nickel plated [SAE AMS QQ N 290]) shell, collet nut, latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular, female
Colour	Grey
Weight	5.45 g
Panel Drill Hole	M7

Environment

Environmental sealing (IP rating)	IP50
Endurance	5000 mating cycles
Temperature range	-55°C / +260°C (max. temperature valid for short periods of use.)
F ret (min)	100 N
Salt Spray Corrosion	>144 hr

https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/eps-00-250-ntn.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Recommended By Lemo

Caps	
Compatible cap	BRE.00.200.NAS
Plastic Cap	BRA.00.200.PCSG
Soft Cap	BEZ.00.200.SCN
Tools	
Spanner 2	DCM.65.088.AZ4
Spanner wrench	Socket for torque wrench DCM.00.M07.4

CAD

Documents	
PCB Eagle	Download