

Cross-Head Phillips Galvanized Screws



Features

- No burrs and sharp edges
- Screw material: 1018 ~ 1022 carbon steel
- Trivalent blue zinc 3.8 μm min. finish
- Heat treat: Case harden surface HV 450 min., core HV 270 ~ 370
- Material and finish comply with 211/65/EU (RoHS)
- Meets DIN 7981 standard

[illegible][illegible]

Thread	D Head Diameter	H Head Height	Type H Drive Size	M (Ref) Drive Width	P	d
ST2.2	3.90~4.20	1.55~1.80	1	2.60	0.8	2.10~2.24
ST2.9	5.30~5.60	1.95~2.20		3.00	1.1	2.76~2.90
ST3.5	6.54~6.90	2.35~2.60	2	4.20	1.3	3.35~3.53
ST3.9	7.14~7.50	2.55~2.80		4.40	1.3	3.73~3.91
ST4.2	7.84~8.20	2.75~3.05		4.60	1.4	4.04~4.22
ST4.8	9.14~9.50	3.25~3.55		5.00	1.6	4.62~4.80
ST5.5	10.37~10.80	3.65~3.95	3	6.50	1.8	5.28~5.46
ST6.3	12.07~12.50	4.25~4.55		7.10	1.8	6.03~6.25

