



### Main

Device application	Distribution Control
Range	Acti9
Product name	Reflex iC60
Device short name	Reflex iC60H
Product or component type	Integrated control circuit breaker
Poles description	3P
Number of protected poles	3
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	D

### Complementary




[In] rated current	10 A
Network frequency	50/60 Hz
Breaking capacity code	H
Breaking capacity	30 kA Icu at 220...240 V AC 50/60 Hz conforming to EN/IEC 60947-2 15 kA Icu at 380...415 V AC 50/60 Hz conforming to EN/IEC 60947-2
[Ui] rated insulation voltage	500 V AC
Contact position indicator	Yes
Control type	Remote control by continuous command ON/OFF button Toggle Remote control by pulse
Control signal type	Maintained Maintained very low voltage Impulse
Local signalling	Red LED: fault Flashing LED: device tripped Green LED: device ON Flashing LED: device overheat Flashing LED: device ready
[Uc] control circuit voltage	230 V AC 50/60 Hz 24 V AC 50/60 Hz 48 V AC 50/60 Hz 24 V DC 48 V DC
[Us] rated supply voltage	230 V AC at 50/60 Hz
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
9 mm pitches	11
Height	84 mm
Width	99 mm
Depth	77 mm
Colour	White
Mechanical durability	50000 cycles
Electrical durability	AC-1: 50000 cycles AC 50 Hz
Provision for padlocking	Padlockable
Locking options description	Padlock in OFF position

Earth-leakage protection	Separate block
Product compatibility	With PLC

## Environment

IP degree of protection	IP20 conforming to IEC 60529
Pollution degree	3
Tropicalisation	2
Relative humidity	93 % at 40 °C

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#"> REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	<a href="#"> Yes</a>
China RoHS Regulation	<a href="#"> China RoHS Declaration</a>
Environmental Disclosure	<a href="#"> Product Environmental Profile</a>
Circularity Profile	<a href="#"> End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins