

## STANDARD 75 OHM COAX BNC TO BNC CABLES



- Van Damme UP-OFC 6.00mm Plasma Grade Standard 75 Ohm cable terminated with Van Damme 2GHz precision BNC connectors
- For analogue video use; also suitable for SMPTE 259M digital video
- Exceptionally flexible cable
- Supplied with Orange strain relief boots
- Hand assembled in the UK
- RoHS Compliant

### COMPONENT PARTS

#### Van Damme UP-OFC 6.00mm Plasma Grade Standard 75 Ohm cable

Electrical Characteristics:

Impedance at 10MHz                      75 Ohms  $\pm$  2

Attenuation

10 MHz	4.21 dB/100m
100 MHz	13.32 dB/100m
135 MHz	15.08 dB/100m
180 MHz	17.42 dB/100m
200 MHz	18.36 dB/100m
400 MHz	28.11 dB/100m
743 MHz	38.31 dB/100m

#### Van Damme Standard 75 Ohm BNC

- High quality 2GHz rated crimp BNC connector
- Turned nickel plated brass body, gold plated brass centre pin, PTFE insulator
- Meets the requirements of SMPTE 292M (1.5 Gb/s data rate)

### PRODUCT LISTING

MPN (Manufacturer's Part Number)	Description
110-062-000	Van Damme standard 75 BNC to BNC 1m
110-064-000	Van Damme standard 75 BNC to BNC 3m
110-065-000	Van Damme standard 75 BNC to BNC 5m
110-102-000	Van Damme standard 75 BNC to BNC 10m
110-104-000	Van Damme standard 75 BNC to BNC 20m