

Parker Product Datasheet



Parker Legris PFA tubing offers 10 times greater durability than other fluoropolymer tubings under severe chemical and mechanical conditions. This tubing range is available in three material grades, offering perfect compatibility with all applications.

PART NUMBER: 1050T06P13
TUBE I.D. (MM): 4
LENGTH (M): 50
TUBE O.D. (MM): 6
COLOR: RED CRYSTAL
TUBING MATERIAL: PFA COLOURED

PRODUCT OVERVIEW

Parker Legris PFA tubing offers 10 times greater durability than other fluoropolymer tubings under severe chemical and mechanical conditions. This tubing range is available in three material grades, offering perfect compatibility with all applications.

Features/Benefits:

- Great Versatility

- Exceptional chemical inertia

- A flexible alternative to stainless steel tubing
- Broad range of working temperatures, from cryogenic to extreme heat
- Non-stick properties allowing conveyance of many fluids & gases
- Outstanding resistance to ageing
- Fluoropolymer with the lowest permeability
- Non-flammable
- UV-transparent
- Tube marking on request
- Silicone-free

- Three Material Grades

- Clear PFA: to cover all applications, including those requiring maximum mechanical resistance
- Colored PFA: for circuit identification
- Black Antistatic PFA: eliminates all risk of electrostatic discharge

Markets:

- Food and Beverage
- Power Generation Equipment
- Aircraft
- Pharmaceutical
- Medical
- Oil and Gas

Applications:

- Applications Subjected to Severe Mechanical and Chemical Conditions
- Medical Fluids Conveying
- Gas and Compressed Air Conveying
- Applications Requiring Very Low and High Temperature
- Fire Hazard Zones
- Applications Subjected to Intensive Cleaning
- Suitable for Fuel Cells and Clean Rooms
- Thermal Management

Technologies:

- Fluoropolymer Tubing
- PFA Tubing
- Perfluoro alkoxy Tubing
- Anti Static Tubing
- Industrial Tubing

TECH SPECIFICATIONS

APPLICATION

Food Processing

SPECIFICATIONS MET

PED 97/23/EC (Industrial)

SPECIFICATIONS MET

FDA 21 CFR 177.1550 (clear)

MEDIA	Medical Fluids
MAXIMUM OPERATING PRESSURE	33 bar
SPECIFICATIONS MET	REACH 1907/2006 (Industrial)
MEDIA	Food & Beverage
SPECIFICATIONS MET	UL 94 V-0 (Fire Resistance, Industrial)
MEDIA	Industrial Gases
MAXIMUM OPERATING TEMPERATURE	150 °C See the Graph “Working Pressure/Working Temperature”
SPECIFICATIONS MET	RoHS 2002/95/EC, 2011/65/EC (Industrial)
MEDIA	Compressed Air
APPLICATION	Aircraft
APPLICATION	Oil & Gas
APPLICATION	Medical
VACUUM PRESSURE RATING	755 mm-Hg
APPLICATION	Pharmaceutical
APPLICATION	Chemicals
DIVISION	Low Pressure Connectors Europe Division
APPLICATION	Clean Rooms
WEIGHT	1.839 kg/package
SPECIFICATIONS MET	USP Class VI (A). Medical: External Communication Devices
MINIMUM OPERATING TEMPERATURE	-40 °C