

Specifications for BMP71 Label Printer Labels

Adhesive	Permanent Acrylic
After Process	Yes, this material will work with this application
Application	Circuit Board & Component Identification; Laboratory Identification
Approval/Compliance	UL Recognised;CSA Accepted;AGA Approved;Halogen Free (DIN VDE 0472/part 815)
Article No.	115111
Board Application	Through Hole - Top
Brady Material No.	B-423
Material Type	Polyester
Brand	WorkHorse™ Series
Colour	White
Environment	Freezer; Autoclave
Finish	Gloss
Laboratory Application	Bottles, Flasks & Dishes;Conical & Large Tubes;Petri Dishes;Well Plates
Description	BradyBondz™ Labels for the BMP™71 Label Printer. Please Note: This material is UL, CSA & AGA approved with its respective ribbon. See the Recommended Ribbon Series for the appropriate ribbon to use.
Max. Characters per Line	20
Max. Lines of Text	5
Max. Service Temp. °C	110
Order Reference	M71-17-423
Printer Compatibility	BMP71
Ribbon Series	M71-R6000HF
Shape	Rectangle
Size - Height (mm)	12.70
Size - Width (mm)	25.40
Surface Mount Technology SMT	No, this material does not work with this application

Through Hole Technology	Top: Yes. In extreme high temperatures, testing of this material is recommended, Bottom: No
Total Qty per Pack	500 Label(s) / Box
Vertical Repeat (mm)	15.88
Vial/Tube (ml)	50.0 ml
Industry	Electronics;Healthcare;Laboratory
Min. Service Temp. °C	-70
QTY. per Row	1
Thickness (mm)	0.0762