

PRODUCT FEATURE & BENEFITS

779.889ILPB / INSPECTION LIGHTS

1. INSPECTION LIGHT - LED 5W COB / 420 Lumens

Lumens

Provides bright, focused illumination in dark or hard-to-reach areas, making it easier to spot issues or perform detailed work.

2. TORCH LIGHT - 1W SMD LED / 45 Lumens

Adds focused, portable illumination, increasing the tool's versatility and usefulness ideal for pinpointing specific spots, looking into tight spaces, or searching for small objects.

3. TWO HOOK CLAMPS

Allows to hang the light in various positions and on different surfaces, increasing stability and versatility for different tasks and environments.



IP30 / IK07



4. MAGNET ONE

Increase stability, flexibility, and convenience, making the tool more effective and user-friendly in various work environments.

5. 180° SWIVEL BASE

Allows to easily adjust the angle of the light up to 180°, offering a flexible, hands-free, and precise lighting, making it easier and more comfortable to illuminate any workspace or hard-to-reach area.

6. MAGNET TWO

Increase stability, flexibility, and convenience, making the tool more effective and user-friendly in various work environments.

7. BATTERY LEVEL INDICATOR

Supplied with USB-C Cable
Run time from 3 to 35 Hours



SKU	SKU Desc	EAN Code	RRP
779.889ILPB	FOLDABLE INSPECTION LIGHT	3662424179648	€xx.xx