



FAG



S6009-2RSR-HLC

Deep groove ball bearing

Deep groove ball bearing S60...-2RSR, corrosion-resistant materials, single row, seals, steel sheet metal cage

Schaeffler ID:
0539676580000

Technical information



Your current product variant

Logistical code	HLC	-
Material Bearing	S	Stainless steel
Sealing	2RSR	Contact seal on both sides
Cage	JN	Steel sheet metal
Tolerance class	PN	Normal (PN)
Dimensional / heat stabilization	SN	Rings dimensional stabilized up to 120°
Lubricant	Lubricating grease	
Radial internal clearance	CN (Group N)	Normal internal clearance
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	45 mm	Bore diameter
D	75 mm	Outside diameter
B	16 mm	Width
C _r	17.800 N	Basic dynamic load rating, radial
C _{0r}	12.100 N	Basic static load rating, radial
C _{ur}	870 N	Fatigue load limit, radial
n _G	4.900 1/min	Limiting speed
≈m	0,243 kg	Weight



Mounting dimensions

$d_{a\min}$	49,6 mm	Minimum diameter shaft shoulder
$D_{a\max}$	70,4 mm	Maximum diameter of housing shoulder
$r_{a\max}$	1 mm	Maximum fillet radius

Dimensions

$r_{\min}$	1 mm	Minimum chamfer dimension
D_2	69 mm	Caliber diameter outer ring
d_1	54,5 mm	Shoulder diameter inner ring

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	100 °C	Operating temperature max.

Calculation factors

f_0	15,2	Calculation factor
-------	------	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Lifetime lubrication, freedom from maintenance
	Grease Lubrication
	Sealed on both sides
	Protected against rust