



Connectors > Circular Connectors > Standard Circular Connectors



Connector System: **Wire-to-Wire**

Sealable: **No**

Connector & Contact Terminates To: **Wire & Cable**

Hermetically Sealed: **No**

Contacts Preloaded: **No**

Features

Product Type Features

Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Contacts Preloaded	No
--------------------	----

Body Features

Environmental Protection	Without
Hermetically Sealed	No

Contact Features

Circular Connector Contact Type	Socket
---------------------------------	--------

Mechanical Attachment

Mating Alignment	Without
Mating Retention	Without

Operation/Application

--



Shielded	No
----------	----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (1.6% in 74013260) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | NECTOR M Series



Connector Hardware(3)



Standard Circular Connectors(45)

Customers Also Bought



TE Part #1-2379240-1
NECTOR T, INLINE PIN, CRIMP, Key-A, S2



TE Part #2359420-1
NECTOR T, T-SPLITTER, Key-A



TE Part #1-2379239-1
NECTOR T, INLINE SOCKET, CRIMP, Key-A,S2

Documents

Product Drawings

NECTOR M SKT CTC BRASS TIN PLTD

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-293475-2_G.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-293475-2_G.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-293475-2_G.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

Agency Approval Document

English

Agency Approval Document

English

Agency Approval Document

English

