



**Part Number: 5200UE**

Security & Sound, 2 Conductor 16 AWG, BC, CMR

**Product Description**

Security & Commercial Audio Cable, Riser-CMR, 2-16 AWG stranded bare copper conductors with polyolefin insulation, PVC jacket with ripcord

**Technical Specifications**

**Product Overview**

Environmental Space:	Indoor - Riser
Suitable Applications:	Data Circuits, Monitor/Detection, Control Circuits, Initiating Circuits, Notification Circuits

**Physical Characteristics (Overall)**

**Conductor**

AWG	Stranding	Material	No. of Conductors
16	19x29	BC - Bare Copper	2

Conductor Count:	2
Conductor Size:	16 AWG

**Insulation**

Material	Nominal Wall Thickness
PP - Polypropylene	0.008 in

**Color Chart**

Number	Color
1	Black
2	Red

**Outer Shield Material**

Material
Unshielded

**Outer Jacket Material**

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	0.184 in	0.017 in	Yes

**Construction and Dimensions**

**Cabling**

Lay Direction	Twists
Left Hand	3 twist/ft

**Electrical Characteristics**

**Conductor DCR**

Nominal Conductor DCR
4.2 Ohm/1000ft

**Capacitance**

<b>Nom. Capacitance Conductor to Conductor</b>
23 pF/ft

#### Inductance

<b>Nominal Inductance</b>
0.14 $\mu$ H/ft

#### Current

Element	Max. Recommended Current [A]
10C Temperature Rise	Per conductor @ 25°C ambient: 6.25 A

#### Voltage

<b>UL Voltage Rating</b>
300 V RMS

#### Temperature Range

UL Temp Rating:	75°C
Operating Temp Range:	-20°C To +75°C

#### Mechanical Characteristics

Bulk Cable Weight:	24 lbs/1000ft
Max Recommended Pulling Tension:	59 lbs
Min Bend Radius/Minor Axis:	2.0 in

#### Standards

NEC Articles:	800
NEC/(UL) Specification:	CMR
CEC/C(UL) Specification:	CMG
CPR Euroclass:	Eca

#### Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

#### Suitability

Suitability - Indoor:	Yes
-----------------------	-----

#### Flammability, LS0H, Toxicity Testing

C(UL) Flammability:	FT4
UL Flammability:	UL1666 Vertical Riser
UL voltage rating:	300 V RMS

#### Plenum/Non-Plenum

Plenum (Y/N):	N
Plenum Number:	6200UH

#### Part Number

#### Variants

Item #	Color	Footnote
5200UE 0101000	Black	
5200UE 010U1000	Black	
5200UE 010Z1000	Black	

5200UE 010Z1000	Black	
5200UE 0061000	Blue, Light	
5200UE 0061000	Blue, Light	
5200UE 001U1000	Brown	
5200UE 001Z1000	Brown	
5200UE 001Z1000	Brown	
5200UE.00152	Chrome	
5200UE.00305	Chrome	
5200UE.00153	Chrome	
5200UE 0081000	Gray	C
5200UE 008500	Gray	
5200UE 008U1000	Gray	
5200UE 008U500	Gray	
5200UE 008Z1000	Gray	
5200UE 008Z1000	Gray	
5200UE 0051000	Green, Dark	
5200UE 0051000	Green, Dark	
5200UE 0031000	Orange	
5200UE 0031000	Orange	
5200UE 0021000	Red	C
5200UE 0021000	Red	C
5200UE 002Z1000	Red	
5200UE 002Z1000	Red	
5200UE 0071000	Violet	
5200UE 0071000	Violet	
5200UE 009U1000	White	
5200UE 0091000	White	
5200UE 0091000	White	
5200UE 009Z1000	White	
5200UE 009Z1000	White	
5200UE 0041000	Yellow	
5200UE 0041000	Yellow	

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.