

Features

- Flexible and durable H05VVH3G1.5- pvc cable
- European plug VIIG-CEE (7) Straight Plug
- Moulded IEC -C19 Connector
- Fully moulded connectors for strength and durability
- Integrated strain relief for connection support and protection

RS PRO 2.5m Power cable C19, IEC to VIIG CEE (7) 16 A 250 V

RS Stock No: 0558952



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- From RS PRO a high quality and durable power cord for connecting an appliance to a mains power supply. This power cord is fully equipped with a right-angled type VIIG CEE (7) European plug on one end and an IEC C19 type connector on the end that connects to the appliance. The power lead features integrated strain relief that provide additional protection and support to the connector.

General Specifications

Connector A	C19, IEC Female – Straight EN60320 /C19
Connector B	CEE (7) VIIG Male – Straight
Sheath Colour	Black
Material	PVC
Applications	IEC C19 were designed to be utilized in high power situations, such as Home Appliances, data centres, servers, network switches and uninterruptible power supplies (UPS) and professional food equipment.

Mechanical Specifications

Length	2.5m
--------	------

Electrical Specifications


Power Cord Rating	16 A - 250V
Visual Inspection	100%
Electrical Test	100%
High pot test wire to wire	3k Vac for 2 sec.
Continuity test	25Aac to grounding / 20Aac to line and neutral
Polarity test	yes
Skin high pot test	6k Vac line to skin

Protection Category

Environmental Conformity	Eu-Directive 2002/96/EC (WEEE)
	Eu-Directive 2003/11/EC (Council Directive 76/769/EEC)
	Eu-Directive 2002/95/EC (RoHS-Compliant)

Approvals

C19 CONNECTOR	ENEC, CE
VII CEE (7)	VDE, OVE, CEBEC, KEMA, S, D, N, LCIE, IMQ, K.
Cable	Harmonised <HAR>



All dimensions in mm