




Connectors > Connector Accessories > Connector Strain Relief



Strain Relief Accessory Type: **Clam Shell**

Primary Product Material: **Thermoplastic**

Compatible With Connector Shell Size: **4**

Shielded: **No**

Thread Size: **14702**

Features

Product Type Features

Strain Relief Accessory Type	Clam Shell
------------------------------	------------

Body Features

Cable Exit Angle	180°, 45°
Primary Product Material	Thermoplastic

Mechanical Attachment

Thread Size	14702
-------------	-------

Housing Features

Compatible With Connector Shape	D-Shaped
Body Orientation	Straight

Dimensions

Compatible Insulation Diameter Range	12.45 mm[.49 in]
--------------------------------------	------------------

Operation/Application

Compatible With Connector Shell Size	4
Shielded	No

Packaging Features

Packaging Method	Bag
Packaging Quantity	1

Product Compliance



For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5205731-1
CLAMSHELL ASSEMBLY



TE Part # 5205979-1
FILLISTER HEAD SCREW,ZN



TE Part # 205723-1
CABLE CLAMP HSG

Also in the Series | [AMPLIMITE Kit](#)



Connector Caps & Covers(2)

Connector Hardware(91)

Connector Seals & Cavity Plugs(4)

Connector Strain Relief(126)

Customers Also Bought

TE Part #2-5767004-7
MICTOR RECEPT ASSY, 228 POS.

TE Part #1-316132-2
DYNAMIC D-3200 HDR ASSY 5P V

TE Part #1318697-2
DYNAMIC D-5 SERIES REC CONTACT

TE Part #102548-5
MOD IV RECP PLTD 30 SEL

TE Part #2345834-2
NEW MOTOR CONN REC KIT. PF

TE Part #1-179552-4
DYNAMIC D-3200S TAB HSG 4P K/X

TE Part #2-5767004-5
MICTOR RECEPT ASSY, 152 POS.

TE Part #225791-2
COAXIAL RF SOCKET, SZ 5

TE Part #1609989-2
16BCF10=F8233

TE Part #87733-1
20 MODIV HSG W/STR RLF DR MRKD

Documents

Product Drawings
CLAMSHELL SIZE 4

English

CAD Files
3D PDF

3D

Customer View Model
ENG_CVM_CVM_5206478-4_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_5206478-4_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5206478-4_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMPLIMITE Subminiature D Connectors - Cable Connectors](#)

English

[AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[Instruction Sheet \(U.S.\)](#)

English