

SITOR fuse-disconnector 22x 58, Up to 100 A, 690 V AC



Model	
product brand name	SITOR
product designation	SITOR fuse switch disconnecter
design of the actuating element	swivel knob
General technical data	
number of poles	3
size of fuse link	22x58
utilization category	AC20B/690 V
size of the fuse link	22 x 58 mm
operating voltage	
• at AC rated value maximum	690 V
• at DC rated value maximum	800 V
Protection class	
protection class IP on the front	IP20
Main circuit	
operational current rated value	100 A
Suitability	
suitability for use main switch	No
suitability for use switch disconnecter	Yes
suitability for use EMERGENCY OFF switch	No
suitability for use safety switch	Yes
Product function	
product function fuse monitoring	No
Short circuit	
conditional short-circuit current (I _q) rated value	100 kA
Connections	
connectable conductor cross-section solid	
• minimum	4 mm ²
• maximum	50 mm ²
type of electrical connection for main current circuit	screw-type terminals
Mechanical Design	
height	117 mm
depth	72.5 mm
fastening method	
• floor mounting	No
• rail mounting	No
net weight	477 g
Approvals Certificates	
General Product Approval	



other

Environment

[Confirmation](#)



[Environmental Con-
firmations](#)

[Environmental Con-
firmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NC2293>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NC2293>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NC2293


CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





last modified:

4/12/2025 [↗](#)

