


**MS4-LFX**  
Activated carbon filter

**FESTO**

Operating instruction



8206835

8206835  
2025-03d  
[8206837]

Original instructions

## Table of contents

<b>1</b>	<b>Applicable documents</b> .....	<b>5</b>
<b>2</b>	<b>Safety</b> .....	<b>5</b>
2.1	Safety instructions.....	5
2.2	Intended use.....	5
2.3	Training of qualified personnel.....	5
<b>3</b>	<b>Additional information</b> .....	<b>5</b>
<b>4</b>	<b>Product design</b> .....	<b>6</b>
<b>5</b>	<b>Mounting</b> .....	<b>6</b>
<b>6</b>	<b>Installation</b> .....	<b>6</b>
<b>7</b>	<b>Commissioning</b> .....	<b>6</b>
<b>8</b>	<b>Maintenance</b> .....	<b>7</b>
8.1	Changing filter.....	7
8.2	Cleaning.....	7
<b>9</b>	<b>Fault clearance</b> .....	<b>7</b>
<b>10</b>	<b>Technical data</b> .....	<b>8</b>
10.1	Technical data, general.....	8
10.2	Technical data, pneumatic.....	8



## 1 Applicable documents



All available documents for the product → [www.festo.com/sp](http://www.festo.com/sp).

## 2 Safety

### 2.1 Safety instructions

- Only use the product in its original condition without unauthorised modifications.
- Only use the product if it is in perfect technical condition.
- Observe the identifications on the product.
- Store the product in a cool, dry environment protected from UV and corrosion. Keep storage times short.
- Take into account the ambient conditions at the location of use.
- Before working on the product, switch off the compressed air supply and lock it to prevent it from being switched on again.
- Use only media to which the materials used for the product are resistant. For evaluation of the media resistance → [www.festo.com/sp](http://www.festo.com/sp).

### 2.2 Intended use

The activated carbon filter removes liquid and gaseous oil components from the compressed air as it passes through.

### 2.3 Training of qualified personnel

Work on the product may only be carried out by qualified personnel who can evaluate the work and detect dangers. The qualified personnel have knowledge and experience in pneumatics.

## 3 Additional information

- Contact the regional Festo contact if you have technical problems → [www.festo.com](http://www.festo.com).
- Accessories and spare parts → [www.festo.com/catalogue](http://www.festo.com/catalogue).

## 4 Product design




Fig. 1: Product design

## 5 Mounting

### Wall mounting

Requirements:

- Space required above the product:  $\geq 30$  mm
- Space required under the product:  $\geq 75$  mm
- Shut-off valves are installed in the compressed air supply line.

1. Align the product vertically in the flow direction from 1 to 2. The numbers on the housing are provided for orientation.
2. Mount the product on the mounting surface with the mounting accessories  
→ 3 Additional information.

## 6 Installation

1. Use fittings, seals and suitable tubing from the Festo catalogue → 3 Additional information.
2. Remove potential dirt particles in the supply lines by blowing out the pipes and hoses. This protects the product from premature failure or higher wear.
3. Screw the fittings into the pneumatic ports.
4. Insert suitable tubing into the fitting to the stop.
  - Position the tubing axial to the pneumatic ports.

## 7 Commissioning

- Slowly pressurise the system.
  - Observe the permissible pressure ranges → 10.2 Technical data, pneumatic. The input pressure  $p_1$  should always be at least 0.05 MPa (0.5 bar; 7.3 psi) higher than the set output pressure  $p_2$ .

## 8 Maintenance

### 8.1 Changing filter



Replace the filter cartridge if the flow rate is reduced even though the pressure setting is unchanged.

1. Exhaust the product.
2. Pull down the release button on the filter bowl.
3. Turn the filter bowl anticlockwise (as seen from below) until the stop can be felt.
4. Remove the filter bowl from the housing.
5. Unscrew the filter anticlockwise.
6. Hold the new filter at the bottom and screw it into the housing clockwise.  
Maximum tightening torque: 1.5 Nm
7. Mount the filter bowl:
  - Align the release button of the filter bowl with the cutout on the housing and insert it.
  - Turn the filter bowl clockwise until the lock audibly engages at the stop.

### 8.2 Cleaning

- Clean the outside of the product as required with a soft cloth.  
Permissible cleaning agents:
  - Soap solution, maximum +60 °C
  - Petroleum ether, free of aromatic compounds

## 9 Fault clearance

Malfunction	Cause	Remedy
Low flow rate. The operating pressure drops with air consumption.	The compressed air supply line is constricted.	– Check the compressed air supply line.
	The filter cartridge is dirty.	– Replace the filter cartridge.

Tab. 1: Fault clearance

## 10 Technical data

### 10.1 Technical data, general

MS4-LFX	
Certificates, declaration of conformity	→ <a href="http://www.festo.com/sp">www.festo.com/sp</a>
Mounting position [°]	Vertical ± 5
Storage temperature [°C]	-10 ... +60
Temperature of medium [°C]	+5 ... +30
Ambient temperature [°C]	-10 ... +60
Pneumatic port 1	
MS4-LFX-1/8	G 1/8
MS4-LFX-1/4	G 1/4
MS4-LFX-AGA	G 1/8
MS4-LFX-Terms and Conditions	G 1/4
MS4-LFX-AGC	G 3/8
Pneumatic port 2	
MS4-LFX-1/8	G 1/8
MS4-LFX-1/4	G 1/4
MS4-LFX-AGA	G 1/8
MS4-LFX-Terms and Conditions	G 1/4
MS4-LFX-AGC	G 3/8

Tab. 2: Technical data, general

### 10.2 Technical data, pneumatic

MS4-LFX	
Operating medium	Compressed air to ISO 8573-1:2010 [3:4:2]
	Inert gases
Information on the operating medium	Not compatible with ester oil
Operating pressure	[MPa] 0 ... 1.4
	[bar] 0 ... 14
	[psi] 0 ... 203

Tab. 3: Technical data, pneumatic



**Festo SE & Co. KG**

Ruiter Straße 82

73734 Esslingen

Germany

Phone: +49 711 347-0

[www.festo.com](http://www.festo.com)