

AGILA LIGHT

1470PAO100P30-11

EAN 4031582331509



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ● ○

CORE ATTRIBUTES

Product Name	Agila light
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	70 kg
Electric Conductive	No
Stainless	No
Load capacity Static	140 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	125 mm
Overall width	44 mm
Overall weight	0.26 kg

HOUSING

Housing Material	Steel sheet, light
Fork shape	Broad
Swivel Bearing	Two ball races
Housing Color	Blue passivated
Offset	28 mm
Swivel radius	78 mm
Swivel interference	156 mm
Dome diameter	41 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Polyurethane, injected
Bearing	Plain bearing
Wheel Color	Silver grey (RAL7001)
Threadguards	Without threadguard
Diameter	100 mm
Tread width	25 mm
Body width	25 mm
Hardness of tread (A)	91 Shore A
Hardness of tread (D)	40 Shore D

FITTING

Fitting type	Bolt hole
Bolt hole diameter	11 mm
Hint	Castors can be mounted with standard screws of any length.