
KEMET Part Number: ALT22A471DD385 Not for New Design

(A663HJ471M385A)



ALT22, Aluminum Electrolytic, 470 uF, 20%, 385 VDC, -40/+85°C



Dimensions		
D	40mm +/-1mm	
L	55mm +/-2mm	
S	10mm +/-0.1mm	
LL	10mm +/-0.5mm	

Packaging Specifications		
Weight:	95 g	
Sleeving:	Yes	
Packaging:	Bulk, Bag	

General Information	
Supplier:	KEMET
Series:	ALT22
Dielectric:	Aluminum Electrolytic
Description:	Solder Tag, Aluminum Electrolytic
Features:	Solder Tag
RoHS:	Yes
Lead:	2 Flying Leads Solder Tags
AEC-Q200:	No
Notes:	Dimensions D And L Include Sleeving

Specifications		
Capacitance:	470 uF	
Capacitance Tolerance:	20%	
Voltage DC:	385 VDC, 423.5 VDC (Surge)	
Temperature Range:	-40/+85°C	
Rated Temperature:	85°C	
Life:	26000 Hrs	
Leakage Current:	1086 uA (5min 20°C)	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

