

Eaton 269236

Catalog Number: 269236

Eaton Moeller series NZM - Molded Case Circuit Breaker. Circuit-breaker, 3p, 125A, H2-A125-NA



General specifications

Product Name

Eaton Moeller series NZM molded case
circuit breaker thermo-magnetic

Catalog Number

269236

EAN

4015082692360

Product Length/Depth

149 mm

Product Height

195 mm

Product Width

105 mm

Product Weight

2.39 kg

Compliances

RoHS conform

Certifications

UL listed

UL 489

CSA-C22.2 No. 5-09

UL/CSA

IEC 60947-2

CE marking

CSA (File No. 22086)

IEC

UL (Category Control Number DIVQ)

UL (File No. E31593)

CSA certified

IEC/EN 60947

Specially designed for North America

CSA (Class No. 1432-01)

Product specifications

Type

Circuit breaker

Special features

Maximum back-up fuse, if the expected short-circuit currents at the installation location exceed the switching capacity of the circuit breaker (Rated short-circuit breaking capacity I_{cn})
Rated current = rated uninterrupted current: 125 A
Switches conform to UL/CSA as well as the IEC regulations. IEC switching performance values are contained on the rating plate.
Adjustable overload releases I_r

Application

Branch circuits, feeder circuits
Use in unearthed supply systems at 690 V

Amperage Rating

125 A

Voltage rating

690 V - 690 V

Circuit breaker frame type

NZM2

Features

Motor drive optional
Protection unit

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Resources

Brochures

[eaton-digital-nzm-brochure-br013003en-en-us.pdf](#)

[eaton-feerum-the-whole-grain-solution-success-story-en-us.pdf](#)

Catalogs

[eaton-digital-nzm-catalog-ca013003en-en-us.pdf](#)

Characteristic curve

[eaton-circuit-breaker-nzm-mccb-characteristic-curve-040.eps](#)

[eaton-circuit-breaker-current-nzm-mccb-characteristic-curve-005.eps](#)

[eaton-circuit-breaker-nzm-mccb-characteristic-curve-050.eps](#)

Drawings

[eaton-circuit-breaker-switch-nzm-mccb-dimensions-017.eps](#)

[eaton-circuit-breaker-nzm-mccb-dimensions-019.eps](#)

[eaton-circuit-breaker-switch-nzm-mccb-3d-drawing.eps](#)

eCAD model

[ETN.269236.edz](#)

Installation videos

[Introduction of the new digital circuit breaker NZM](#)

[The new digital NZM Range](#)

mCAD model

[DA-CD-nzm2_3p](#)

[DA-CS-nzm2_3p](#)

Technical data sheets

[eaton-nzm-technical-information-sheet](#)

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

Pollution degree

3

Mounting Method

Fixed

Built-in device fixed built-in technique

DIN rail (top hat rail) mounting optional

Climatic proofing

Damp heat, cyclic, to IEC 60068-2-30

Damp heat, constant, to IEC 60068-2-78

Equipment heat dissipation, current-dependent

27.61 W

Utilization category

A (IEC/EN 60947-2)

Isolation

300 V AC (between the auxiliary contacts)

500 V AC (between auxiliary contacts and main contacts)

Ambient operating temperature - max

70 °C

Ambient operating temperature - min

-25 °C

Ambient storage temperature - max

70 °C

Ambient storage temperature - min

40 °C

Low-voltage HBC fuse - max

355 A gG/gL

Number of auxiliary contacts (change-over contacts)

0

Number of auxiliary contacts (normally closed contacts)

0

Number of auxiliary contacts (normally open contacts)

0

Protection against direct contact

Finger and back-of-hand proof to DIN EN 50274/VDE 0106 part 110

Degree of protection

IP20 (basic degree of protection, in the operating controls area)
IP20

Direction of incoming supply

As required

Electrical connection type of main circuit

Screw connection

Lifespan, mechanical

20000 operations

Overvoltage category

III

Rated operational current

300 A (415 V AC-1, making and breaking capacity)
125 A (660-690 V AC-3, making and breaking capacity)
125 A (690 V AC -1, making and breaking capacity)
300 A (380/400 V AC-1, making and breaking capacity)

Degree of protection (IP), front side

IP66 (with door coupling rotary handle)
IP40 (with insulating surround)

Degree of protection (terminations)

IP00 (terminations, phase isolator and strip terminal)
IP10 (tunnel terminal)

Number of poles

Three-pole

Terminal capacity (copper strip)

Min. 2 segments of 9 mm x 0.8 mm at box terminal
Max. 10 segments of 16 mm x 0.8 mm at box terminal
Min. 2 segments of 16 mm x 0.8 mm at rear-side connection
(punched)
Max. 10 segments of 16 mm x 0.8 mm at rear-side connection
(punched)

Lifespan, electrical

6500 operations at 415 V AC-3
6500 operations at 400 V AC-3

7500 operations at 690 V AC-1
10000 operations at 400 V AC-1
5000 operations at 690 V AC-3

Functions

Current limiting circuit breaker
System and cable protection

Shock resistance

20 g (half-sinusoidal shock 20 ms)

Position of connection for main current circuit

Front side

Rated operational current for specified heat dissipation (I_n)

125 A

Power loss

27.6 W

Release system

Thermomagnetic release

Short-circuit total breaktime

< 10 ms

Rated short-time withstand current (t = 0.3 s)

1.9 kA

Rated short-time withstand current (t = 1 s)

1.9 kA

Short-circuit release non-delayed setting - max

1250 A

Short-circuit release non-delayed setting - min

750 A

Terminal capacity (control cable)

16 mm² - 18 mm² (2x)

14 mm² - 18 mm² (1x)

Terminal capacity (copper busbar)

Min. 16 mm x 5 mm direct at switch rear-side connection

Max. 20 mm x 5 mm direct at switch rear-side connection

M8 at rear-side screw connection

Terminal capacity (copper solid conductor/cable)

6 mm² - 12 mm² (1x) at box terminal

16 mm² (1x) at tunnel terminal

6 mm² - 11 mm² (1x) direct at switch rear-side connection

Terminal capacity (aluminum solid conductor/cable)

16 mm² (1x) at tunnel terminal

Terminal capacity (copper stranded conductor/cable)

4 mm² - 350 mm² (1x) at box terminal

4 mm² - 350 mm² (1x) at tunnel terminal

4 mm² - 3/0 mm² (1x) direct at switch rear-side connection

Handle type

Rocker lever

Short delay current setting (I_{sd}) - max

0 A

Short delay current setting (I_{sd}) - min

0 A

Instantaneous current setting (I_i) - max

1250 A

Instantaneous current setting (I_i) - min

750 A

Number of operations per hour - max

120

Overload current setting (I_r) - max

125 A

Overload current setting (I_r) - min

100 A

Rated short-circuit breaking capacity I_{cs} (IEC/EN 60947) at 230 V, 50/60 Hz

150 kA

Rated short-circuit breaking capacity I_{cs} (IEC/EN 60947) at 400/415 V, 50/60 Hz

150 kA

Rated short-circuit breaking capacity I_{cs} (IEC/EN 60947) at 440 V, 50/60 Hz

130 kA

Rated short-circuit breaking capacity I_{cs} (IEC/EN 60947) at 525 V, 50/60 Hz

37.5 kA

Rated short-circuit breaking capacity I_{cs} (IEC/EN 60947) at 690 V, 50/60 Hz

5 kA

Rated short-circuit making capacity I_{cm} at 400/415 V, 50/60 Hz

330 kA

Rated short-circuit making capacity I_{cm} at 440 V, 50/60 Hz

286 kA

Rated short-circuit making capacity I_{cm} at 525 V, 50/60 Hz

105 kA

Rated short-circuit making capacity I_{cm} at 690 V, 50/60 Hz

40 kA

Standard terminals

Screw terminal

Rated operating voltage U_e (UL) - max

600Y/347 V, 480 V

Rated short-circuit making capacity I_{cm} at 240 V, 50/60 Hz

330 kA

Rated impulse withstand voltage (U_{imp}) at auxiliary contacts

6000 V

Rated impulse withstand voltage (U_{imp}) at main contacts

8000 V

Rated insulation voltage (U_i)

1000 V AC



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia