



Main

Range of product	Ovalis
Range	Ovalis C Series
Product or component type	Socket-outlet
Socket number	1
Device presentation	Complete product
Outlet poles configuration	2P with shutters
Outlet standard description	Unearthed
Outlet standard deviation	European
Colour tint	White (RAL 9003)
Type of packing	Flow-pack
Quantity per set	10
Sale per indivisible quantity	1
Number of terminals	3

Complementary

Device mounting	Flush
Fixing mode	By claws By screws
Surface finish	Matt
Rated current	16 A at 250 V AC 50/60 Hz
Electrical durability	5000 cycles
Service life in cycles	5000 cycles
Connections - terminals	Screw terminals
Shape of screw head	Pozidriv No 1
Clamping connection capacity	1 x 1.5...2 x 4 mm ² for rigid cable(s) 1 x 1.5...2 x 4 mm ² for stranded cable(s) 1 x 1.5...2 x 4 mm ² for flexible cable(s)
Wire stripping length	12 mm
Surface treatment	Untreated
Material	ASA + PC: mechanism cover PBT (polybutylene terephthalate) GF30: support frame PC (polycarbonate) GF10 FR: casing
Height	87 mm
Width	87 mm
Depth	42.5 mm
Embedding depth	26.5 mm
Net weight	0.047 kg

Environment

Ambient air temperature for storage	-5...50 °C
Dielectric strength	2000 V
Ambient air temperature for operation	5...35 °C
Standards	NF C 61-314
Product certifications	NF
IK degree of protection	IK04
IP degree of protection	IP21D
Environmental characteristic	Acetone Liquid soap UV resistant Bleach Window-cleaning fluid Petrol Alcohol Oil

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations