

## FEATURES

- **Mixture: Propane/ Butane**
- **Appearance: Colourless**
- **Boiling Point: -42 °C**
- **Freezing Point: -188°C**
- **Flammability Limits: 2% – 11% in**
- **Air Auto-ignition Temperature: 450°C**
- **Density 0.5 g/ml**
- **Specific Gravity of Vapour (Air = 1.0) 1.5 at 15 °C**
- **Vapour Pressure 6 – 6.5bar at 15°C, 11 – 12 bar at 55°C**

## RS PRO Gas Torch Refill

RS Stock No.: 790-3583



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

**Product Description**

Introducing a range of propane and butane gas refills from RS PRO. A mixture of propane and butane gases which acts as a fuel designed specifically for your portable gas soldering irons, gas torches and products operated by propane and butane.

**General Specifications**

<b>Accessory Type</b>	Gas Torch Refill
<b>For Use With</b>	Gas Blowtorches
<b>Colour</b>	Colourless
<b>Gas Mixture</b>	Propane/ Butane
<b>Density</b>	0.5 g/ml
<b>Shelf Life</b>	48 Months
<b>Flammability Limits</b>	2 – 11 % in Air
<b>Applications</b>	Cooking or food preparation, Home DIY, Camping and caravanning, Welding, Soldering, Automotive repair and maintenance

**Operation Environment Specifications**

<b>Boiling Point</b>	-42°C
<b>Freezing Point</b>	-188°C
<b>Auto-ignition Temperature</b>	450°C
<b>Specific Gravity of Vapour (Air = 1.0)</b>	1.5 at 15 °C
<b>Vapour Pressure</b>	6 – 6.5 bar at 15 °C; 11 – 12 bar at 55 °C

**Approvals**

<b>Standard Mets</b>	EN417
----------------------	-------

